

37W USB-C & USB-A Wall Charger, Portable Charger with USB Power Delivery Fast Charging, 25W USB-C PD / 12W USB-A Output, Dual-Port USB-C/USB-A

Product ID: 114NB-WALL-CHARGER



This 37W USB-C and USB-A wall charger delivers fast, efficient charging for the MacBook Neo, iPhones, Android phones, tablets, and other low-power USB-C devices, ideal for travel, hybrid work, or everyday use. The dual-port design provides up to 25W over USB-C and 12W over USB-A, enabling simultaneous charging in a compact form factor.

This small, high-efficiency charger measures 59.8 x 56.3 x 27.7mm and weighs just 97g (3.4oz). With 1.0A input current and a foldable plug, it delivers stable performance in space-conscious or mobile setups.

Charge a wide range of USB-C and USB-A devices including iPhone Pro/Max, iPhone 17, iPad Pro/Air and Samsung Galaxy. The USB-C port supports up to 25W Power Delivery (5V, 9V, 12V, 15V, 20V) with PPS, while the USB-A port provides up to 12W for accessories or secondary devices. It can provide supplemental charging for laptops, like the MacBook Air, when they are not actively being used, such as overnight or between work sessions

Built-in safeguards protect against over-voltage, over-current, and heat. Certified for global use with cULus, FCC/ICES, and Japan PSE approvals.

This charger features a housing made from 75% post-consumer recycled (PCR) material. The product also ships in FSC Mix packaging made from responsibly sourced materials. These materials help align your IT infrastructure with your organization's sustainability goals, without compromising on quality or durability.

Certifications, Reports and Compatibility



Applications

- Enables mobile professionals and hybrid workers to power both a phone and tablet simultaneously from a single compact charger, reducing desk clutter and simplifying travel setups
- Provides IT teams with a certified, ESG-aligned dual-port charging solution for corporate-issued iPhone, iPad, Galaxy, and Pixel devices, supporting safe deployment in regulated or sustainability-focused organizations

Features

- **Charge Devices with 37W Dual-Port Power**: Deliver up to 25W USB-C Power Delivery (5V, 9V) to charge devices such as the MacBook Neo or iPad Pro while a 12W USB-A output (5V) charges iPhones, tablets, and accessories; 37W total combined output
- **Travel Light Without Sacrificing Power**: Compact charger measures 59.8 x 56.3 x 27.7mm and weighs just 97g (3.4 oz), making it easy to carry in laptop bags and mobile work kits
- **Power Two Devices with Stable Performance**: Supports 1.0A input current for consistent operation; USB-C and USB-A ports enable simultaneous device and accessory charging without compromising reliability; Efficient design meets DOE Level VI standards
- **Protect Devices with Certified Safety**: Builtin protection guards against overvoltage, overcurrent, and heat; cULus, FCC/ICES, and Japan PSE certified for global safety; Features 75% postconsumer recycled (PCR) housing and FSCMix certified packaging
- **The IT Pro's Choice**: Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

Hardware

Warranty	2 Years
Ports	2

Connector(s)

Input Connector(s)	1 - 100 - 240 AC
Output Connectors	1 - USB Type-C (24 pin) USB Power Delivery Only
	1 - USB Type-A (4 pin) Power Only

Power

Input Voltage	110V-240V AC
Input Current	1.5 A
Output Voltage	5V DC
	9V DC

	15V DC
	20V DC
Output Current	3 A
Environmental	
Operating Temperature	0 to 25C (32 to 77F)
Storage Temperature	-20 to 85C (-4 to 185F)
Humidity	20% ~ 90% RH
Physical Characteristics	
Color	Black
Product Length	2.2 in [56.4 mm]
Product Width	1.1 in [27.7 mm]
Product Height	2.3 in [59.5 mm]
Weight of Product	3.4 oz [97 g]
Packaging Information	
Package Length	3.1 in [8.0 cm]
Package Width	3.7 in [9.3 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	4.8 oz [135.0 g]
What's in the Box	
Included in Package	1 - Wall Charger 1x USB-A 1x USB-C
Warranty Information	
Warranty	2 Years

***Product appearance and specifications are subject to change without notice.**