2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

Produkt ID: ISAS88702

The ISAS88702 2-meter Serial Attached SCSI Cable is designed for high-performance networks, servers, workstations and desktops. This SAS cable features a SFF-8470 (Infiniband®) connector and a SFF-8088 (external mini-SAS) connector that supports data transfer rates up to 6 Gbps.

The SFF-8470 to SFF-8088 SAS cable is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Connect SAS Controllers to SAS Backplanes
- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures

Funktioner

- Durable metal connectors
- Infiniband® plug with thumbscrews for secure connections

• Supports data transfer rates up to 6 Gbps

• Compatible with many servers, including:
IBMMegaRAID 8480
IBM System Storage EXP3000
IBM x3850 (8864)
IBM x3800 (8866)
IBM x3655 (7985)
IBM x3455 (7984,7986)
IBM x3250 (4364,4365)

Hårdvara		
	Garantipolicy	Lifetime
	Antal ledare	8 Twisted Pair
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kabelskärmning	Aluminiumpolyesterfolie med förtent kopparfläta
Kontakt(er)		
	Connector A	1 - SFF-8470 (32-stifts, InfiniBand, extern SAS)
	Connector B	1 - SFF-8088 (26-stifts, extern Mini-SAS)
Utseende		
	Färg	Svart
	Tråddimension	28 AWG
	Kabellängd	6.6 ft [2 m]
	Diameter	7.874mm
	Produktlängd	6.6 ft [2.0 m]
	Produktbredd	0.0 in [0.0 cm]
	Produkthöjd	0.0 in [0.0 cm]
	Produktvikt	9.5 oz [268.0 g]
Förpackning		
	Förpackningsantal	1
	Package Length	13.0 in [33.0 cm]
	Package Width	10.0 in [25.5 cm]
	Package Height	0.9 in [24.0 mm]

Fraktvikt (förpackning)	9.5 oz [270.0 g]

Vad det är i lådan

Ingår i paketet	1 - 2m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.