1m External Mini SAS Cable - Serial Attached SCSI SFF-8088 to SFF-8088

Product ID: ISAS88881

The ISAS88881 1m External SAS Cable is designed for high-performance networks, servers, workstations and desktops, supporting data transfer rates of up to 6 Gbps.

This durable Mini SAS cable features SFF-8088 to SFF-8088 plugs for connecting your external SAS devices (controllers, hard drives, SAN storage area network, etc.), and it is TAA-compliant for Federal (GSA Schedule) purchases.

Constructed of high quality materials this 1-meter SAS cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

• For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures

• Connect SAS Controllers to SAS Backplanes

• Connect external hard drive to SAS Controller

Features

• 2x SFF-8088 plugs with latches

- Durable metal connectors
- Supports data transfer rates up to 6 Gbps
- Multi-lane design
- Backwards compatible with SATA devices

Hardware		
	Warranty	Lifetime
	Number of Conductors	8 Twisted Pair
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-polyester foil with tinned copper braid
Connector(s)		
	Connector A	1 - SFF-8088 (26-pin, External Mini-SAS)
	Connector B	1 - SFF-8088 (26-pin, External Mini-SAS)
Physical Characteristics		
	Color	Black
	Wire Gauge	28 AWG
	Cable Length	3.3 ft [1 m]
	Product Length	39.4 in [100.0 cm]
	Product Width	1.4 in [3.5 cm]
	Product Height	0.6 in [1.5 cm]
	Weight of Product	5.0 oz [143.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	13.0 in [33.0 cm]
	Package Width	9.8 in [25.0 cm]
	Package Height	0.6 in [1.4 cm]

Shipping (Package) Weight	5.7 oz [161.0 g]

What's in the Box

Included in Package	1 - 1m External Serial Attached SCSI SAS Cable - SFF-8088 to SFF-8088

Product appearance and specifications are subject to change without notice.