

6 ft Transparent IEEE-1394 Firewire Cable 4-6 M/M

**Product ID:** 1394\_46\_6T



This 6ft clear 1394 FireWire cable features a 4-to-6 pin (M-M) configuration that delivers a reliable link for today's demanding FireWire peripheral connections.

The FireWire 400 cable also offers an attractive clear (transparent) sheathing that blends discreetly into any operating environment.

## **Certifications, Reports and Compatibility**

### **Applications**

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

### **Features**

- Transparent color blends into any environment
- Up to 400 Mbits/sec data transfer rate
- Supports Plug and Play
- Hot Pluggable; allows swapping of live devices
- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Supports a daisy-chain of up to 63 firewire devices

- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference

---

**Hardware**

|                    |                        |
|--------------------|------------------------|
| Warranty           | Lifetime               |
| Industry Standards | IEE1394-1995 Compliant |

---

**Performance**

|                      |                 |
|----------------------|-----------------|
| Maximum Cable Length | 14.0 ft [4.3 m] |
|----------------------|-----------------|

---

**Connector(s)**

|             |                                  |
|-------------|----------------------------------|
| Connector A | FireWire 400 (4 pin, IEEE 1394a) |
| Connector B | FireWire 400 (6 pin, IEEE 1394a) |

---

**Physical Characteristics**

|                |                |
|----------------|----------------|
| Color          | Transparent    |
| Cable Length   | 6.0 ft [1.8 m] |
| Product Length | 6.0 ft [1.8 m] |

---

**Packaging Information**

|                           |                  |
|---------------------------|------------------|
| Package Length            | 4.9 in [12.5 cm] |
| Package Width             | 0.5 in [12.8 mm] |
| Package Height            | 8.7 in [22.2 cm] |
| Shipping (Package) Weight | 3.5 oz [100 g]   |

---

**What's in the Box**

|                     |  |
|---------------------|--|
| Included in Package | 6 ft. Transparent FireWire Cable 4-6 Pin |
|---------------------|--|

---

*\*Product appearance and specifications are subject to change without notice.*

