

1 ft IEEE-1394 FireWire Cable 9-6 M/M

Productcode: 139496MM1



This 1ft IEEE 1394 FireWire Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV Camcorder to a computer, etc.).

This 1ft IEEE-1394 FireWire Cable (9-pin to 6-pin) cable provides a means to connect a FireWire 1394b device to a PC that only supports FireWire 1394a and vice versa, without costly upgrades.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together
- Perfect for use with portable FireWire applications

Eigenschappen

- Supports data transfer rates up to 400 Mbps
- Hot Pluggable
- 1394a & 1394b Standards Compliant
- Supports a daisy-chain of up to 63 FireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Prestaties

Type en snelheid	FireWire 400 IEEE-1394a - 400 Mbit/s
------------------	--------------------------------------

Connector(en)

Connector A	1 - Firewire 800 (9-polig, IEEE 1394b)
Connector B	1 - Firewire 400 (6-polig, IEEE 1394a)

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	30 AWG
Kabellengte	1.0 ft [0.3 m]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	4.9 in [12.5 cm]
Package Width	0.5 in [12.5 mm]

Package Height 8.5 in [21.5 cm]

Verzendgewicht
(verpakt) 1.8 oz [50 g]

Wat wordt er
meegeleverd

Meegeleverd 1 - 1 ft IEEE-1394 FireWire Cable 9-6 M/M

Garantiebepalinge
n

Warranty Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.