10ft CAT6 Ethernet Cable - Black CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

ID del Producto: N6PATCH10BK

The N6PATCH10BK Cat 6 Patch Cable (10 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad

Aplicaciones

• Diseñado para utilizar con redes Gigabit

• Permite realizar conexiones desde el concentrador al panel de distribución

• Permite conectar la estación de trabajo a una placa de pared

Características

• Capuchones de color para una codificación departamental por colores

• El alivio de tensión moldeado evita que el cable se doble formando ángulos agudos en el conector RJ45 y de este modo minimiza la tensión en el punto de terminación del enchufe

• Fabricados con componentes de máxima calidad

• Alambre de cobre calibre 24 AWG de alta calidad

• Certificación ETL

• Protectores para clips de conectores RJ45

• Cuidadosamente fabricado y testeado para mantener el Near End Crosstalk (NEXT) dentro de los límites aceptables

---

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)
Tipo de Cable	Libre de Enganches

	Estándar de Cableado	TIA/EIA-568-B.1-2001 T568B
Rendimiento		
	Clasificación de Cables	CAT6 - 650 MHz
Conector(es)		
	Conector A	1 - RJ-45
	Conector B	1 - RJ-45
Características Físicas		
	Color	Negro
	Calibre del Conductor	24 AWG
	Tipo de conductor	Cobre trenzado
	Longitud del Cable	10.0 ft [3.0 m]
	Longitud del Producto	10.0 ft [3.0 m]
	Peso del Producto	4.7 oz [134 g]
Información de la Caja		
	Cantidad de Paquetes	1
	Longitud de la Caja	8.7 in [22 cm]
	Ancho de la Caja	7.9 in [20 cm]
	Altura de la Caja	0.7 in [19 mm]
	Peso (de la Caja) del Envío	5.1 oz [144 g]

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.