24 Port 0.5U Cat5e Patch Panel - RJ45 Ethernet Rackmount Cat 5e 110 Patch Panel

Product ID: PANELHU24

The PANELHU24 Rack Mount Cat5e patch panel condenses 24 ports into a 0.5U panel, making it an ideal solution for smaller installations.

Color coded for both T568A and T568B wiring, this network patch panel provides the perfect solution for any voice or LAN application and offers dual type IDC termination. For convenience, the port numbers are clearly marked on the front of each RJ45 port, offering a quick and easy way to identify cable runs.

Durably constructed of only top quality materials, this 24-port Ethernet patch panel is backed by StarTech.com's 2 year warranty.

Certifications, Reports and Compatibility

Applications

• For installation in 19" rack/cabinets

• Suitable for applications that use 22-26 AWG solid state and standard network cables

• 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications

• Voice, video and other applications

Features

• High impact plastic housing, flame retardant UL 94V-0

• Meets and exceeds ANSI/TIA-568-C.2, ISO/IEC 11801 and EN 50173-1 specifications

• Dual-type IDC headers, situated 180 relative to the RJ45 ports, terminated using 110-type punch tool

• Color coded for both T568A and T568B installations

Special Notes / Requirements		
	Warranty	2 Years
	Note	IDC Contact: 0.8mm thickness alloy, tin plating over nickelJack Contact: phosphor bronze, gold over nickel
Environmental		
	Operating Temperature	-10~50
	Humidity	10~65%
Physical Characteristics		
	Color	Black
	Product Length	19.0 in [482 mm]
	Weight of Product	14.4 oz [409 g]
Packaging Information		
	Package Quantity	1
	Package Length	19.5 in [49.6 cm]
	Package Width	2.4 in [6.1 cm]
	Package Height	1.9 in [47 mm]
	Shipping (Package) Weight	1.1 lb [0.5 kg]
What's in the Box		
	Included in Package	1 - 24 Port 1/2U Rackmount Cat5e 110 Patch Panel
		M6 Screws
		M5 Screws

Zip Ties

1 - Instruction Manual

Product appearance and specifications are subject to change without notice.