1 Port 10/100 Mbps Parallel Network Print Server

Product ID: PM1115P

This 10/100 Mbps Print Server lets you connect a Parallel printer to your Fast Ethernet (10/100Mbps) network, allowing you to share the printer between many networked users, instead of having to purchase separate printers for each individual workstation.

The parallel print server can be installed in minutes and features remote web-based management for simple configuration. The print server features a small footprint design that saves valuable deskspace, and can be connected directly into the parallel printer Centronics port and connected to a Fast Ethernet network using standard network cable (RJ45 terminated).

Providing dependable parallel printer sharing, this 10/100Mbps Print Server is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility

RoHS Compliant

Windows 8 | Windows 7 | Windows Server 2012 | Mac OS Yosemite | Mac OS Mavericks

Applications

• Connects your Ethernet network to one Parallel printer

• PM1115P offers network printing solution for home, small office, educational & government institutions and any

other environments that require printer sharing

Features

• Compact and light weight print server only weighs 2.4 ounces

• Compliant with IEEE 1284, IEEE 802.3 & IEEE 802.3u standards

• Configurable using a Web based browser or a Windows based configuration

• Connects directly to the Centronics port of your printer

• Easy setup and configuration

• Eliminates the need to purchase additional printers for individual workstations

• Share 1 printer with computers connected to a home or small office network

• Support SNMP for remote printer management and works with any SNMP based application to access and manage

• Supports 10/100 Mbps fast Ethernet network

Hardware		
	Warranty	2 Years
	Ports	1
Performance		
	Remote Management Ability	Yes
	Supported Protocols	AppleTalk
		IPX/SPX
		NetBEUI
		SMNP
		TCP/IP
Connector(s)		
	External Ports	1 - Centronics (36 pin)
		1 - RJ-45
Software		
	OS Compatibility	Windows 8 / 8.1 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64),

		2000, ME, 98SE
		Windows Server 2012, 2008 R2, 2003(32/64)
		Mac OS 10.x (Tested up to 10.10)
		Linux
Special Notes / Requirements		
	System and Cable Requirements	Ethernet network cable not included
Indicators		
	LED Indicators	1 - LAN
		1 - Status
		1 - Activity
Power		
	Power Source	AC Adapter Included
	Input Voltage	115V AC
	Output Voltage	7.5 DC
	Output Current	500mA
	Center Tip Polarity	Positive
	Plug Type	M
Physical Characteristics		
	Color	Beige
	Material	Plastic
	Product Length	2.2 in [55 mm]
	Product Width	2.0 in [5 cm]
	Product Height	0.9 in [2.2 cm]
	Weight of Product	2.4 oz [67 g]
Packaging Information		
	Package Length	9.4 in [24 cm]

Package Width	3.1 in [78 mm]
Package Height	6.2 in [15.8 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - Parallel Print Server
	1 - Power Adapter (NA)
	1 - Driver CD
	1 - Instruction Manual

Product appearance and specifications are subject to change without notice.