

Desk Mount Monitor Arm For 27in 16:9 or 30in 21:9 Ultrawide Screens, VESA 75x75/100x100, Tool-Less Mechanical Spring Arm, C-Clamp/Grommet, TAA

Product ID: 1MP1ACG-MONITOR-ARM



This monitor desk mount is designed to support up to 27-inch 16:9 or 30-inch 21:9 display, creating an ergonomic area for productivity. The mechanical spring-assisted arm enables multiple adjustment to suit different ergonomic needs.

The spring arm enables toolless height adjustment of up to 10.6in (270mm) with effortless one-touch motion. Adjust the height of the arm along the 10.2in (261mm) pole. The arm can extend up to 22.2in (590mm) from the pole.

The quick toolless slide and click design makes assembly quick and simple. The pre-assembled desk clamp and pole can be easily secured by hand to the desk, saving total installation time.

The articulating arm enables toolless adjustments of +/-180 horizontal swivel, 105 tilt, 240 pan, and 360 screen rotation on the VESA plate for portrait or landscape orientations. This flexibility enables users to customize the screen placement for maximum productivity and comfort.

With its steel and aluminum construction, the premium monitor arm supports a weight capacity of 19.8 lb. (9 kg). Die-cast aluminum arms with mechanical springs that passed 10,000 cycle test and are backed for 10 years for long-lasting performance.

To maintain an organized workspace, the adjustable arm features a cable management channel along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup. A cable clip on the pole also helps maintain an organized workspace.

Certifications, Reports and Compatibility



Applications

Features

- **DESK MOUNT MONITOR ARM:** Single monitor VESA mount (75x75/100x100mm) supports up to 19.8lb (9kg) 27-inch 16:9 or 30-inch 21:9 ultrawide displays; High-quality mechanical spring tested to 10,000 cycle
- **QUICK AND TOOLLESS ASSEMBLY:** Premium monitor arm with toolless slide & click design, featuring thumb screws, makes assembly quick and simple; Pre-assembled desk clamp & pole can be easily secured by hand to the desk, saving total installation time
- **RANGE OF MOTION:** Ergonomic articulating arm with toolless adjustments of +/-180 horizontal swivel, 105 tilt, 240 pan, and 360 screen rotation for portrait & landscape orientations; TAA-compliant
- **MOUNTING OPTIONS:** Interchangeable desk C-clamp or grommet mount for desks up to 4.3-inches (110mm) thick; Monitor stand includes tools to adjust the arm tension to match the monitor weight; Detachable VESA plates w/quick release mechanism
- **ORGANIZED WORKSPACE:** Computer monitor mount with cable management channels along the arm to keep cables out of sight; A cable clip on the pole helps maintain a tidy setup

Hardware

Warranty	10 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.7 - 4.3 in (20 - 110 mm) Grommet Diameter: 0.4 in - 2.3 in (10 - 60 mm)

Performance

Weight Capacity (Per Display)	19.8 lb [9 kg]
-------------------------------	----------------

Minimum Display Size	17"
Maximum Display Size	30in
Fits Curved Display	No
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Minimum Height	10.6 in [270 mm]
Maximum Height	11.9 in [302 mm]
Minimum Arm Extension	3.1 in [80 mm]
Maximum Arm Extension	23.2 in [590 mm]
Display Tilt	+90 / -15
Display Swivel	+/- 120
Swivel / Pivot	+180 / -180
Display Rotation	+90 / - 90
Anti-theft	No

Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	4.1 in [10.3 cm]
Product Width	26.5 in [67.4 cm]
Product Height	14.2 in [36.1 cm]
Weight of Product	7.9 lb [3.6 kg]

Packaging Information

Package Length	11.6 in [29.5 cm]
Package Width	18.8 in [47.8 cm]
Package Height	5.6 in [14.1 cm]

Shipping (Package) Weight	10.2 lb [4.6 kg]
------------------------------	------------------

What's in the Box

Included in Package	1 - Spring Arm
	1 - Swivel Arm
	1 - Pole Mount Assembly
	1 - VESA Monitor Mount
	1 - Cable Management Clip
	1 - Hex Key
	4 - Monitor Thumbscrews
	1 - Base Cushion
	1 - User Manual

Warranty Information

Warranty	10 Years
----------	----------

****Product appearance and specifications are subject to change without notice.***