8U Sideways Wall-Mount Rack for Servers

Product ID: RK819SIDEM

The RK819SIDEM Side-mounted Wallmount Open Frame Rack/Cabinet is an 8U server rack that lets you mount your (19-inch wide) servers, A/V or network equipment facing perpendicular to the wall, for easy access to mounted devices and equipment. The cabinet/rack features open access to both the front and back of your devices, making it easy to adjust cabling, view LEDs and access configuration buttons as needed. Plus, the nature of the sidemount configuration allows for deeper mounting depths than typical wallmount racks, without causing an obstruction. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality SPCC cold-rolled steel, for strength and durability, the open frame equipment rack allows for maximum airflow while still supporting a maximum weight capacity of 159 kg (350 lbs). The wall mount rack also ships complete with all of the M5 screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

RoHS Compliant

TAA COMPLIANT

CE

Applications

• Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location

• Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

• Mount Audio/Video broadcast or distribution components

Features

• Ships fully assembled and includes all necessary screws/nuts

• TAA compliant for GSA Schedule purchases

• Weight capacity of 350 lb (159 kg)

• Sidemount configuration allows for a greater mounting depth

• Sturdy SPCC cold-rolled steel construction

• Open frame design for optimum airflow

• Wall mount holes are 16" center-to-center, for mounting to any standard wooden studs (easily mounts to concrete or steel as well)

Hardware		
	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	4-Post
	Frame Type	Open Frame
	U Height	8U
	Special Features	Ships Fully Assembled
		Wall-Mountable
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity	350.6 lb [159 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel

Product Measurements		
	Product Length	22.2 in [56.5 cm]
	Product Width	21.2 in [53.8 cm]
	Product Height	19.0 in [48.3 cm]
	Weight of Product	39.8 lb [18.0 kg]
	Maximum Mounting Depth	20.8 in [52.9 cm]
Packaging Information		
	Flat Pack (Assembly Required)	No
	Package Length	23.5 in [59.6 cm]
	Package Width	22.7 in [57.6 cm]
	Package Height	20.4 in [51.7 cm]
	Shipping (Package) Weight	46.3 lb [21.0 kg]
What's in the Box		
	Included in Package	1 - 8U Rack
		36 - M5 Screws
		36 - M5 Cage Nuts

Product appearance and specifications are subject to change without notice.