2m USB-C to HDMI Adapter Cable, Gripping HDMI Connector, 4K 60Hz, Thunderbolt Compatible, HDR, Uni-Directional Cord for MacBook, Dell, HP, Lenovo

Product ID: 2M-USBC-HDMI-4K60-G



Connect USB-C laptops to 4K 60Hz HDMI displays with a single 2m active adapter cable that delivers stable, high-bandwidth video and audio for professional workspaces.

Avoid costly interruptions in boardrooms, hot desks, and collaboration areas. The gripping HDMI connector resists vibration and strain, helping maintain a secure connection to the display even when cables are frequently connected and disconnected.

Speed up installs with clear markings on the connector that verify the HDMI cables capabilities at a glance. Drive HDR-ready 4K 60Hz video with full 4:4:4 / RGB color and 7.1-channel audio for clear text and visuals. The integrated cable and adapter design reduces signal loss, cuts down on clutter, and removes common failure points.

Roll out instantly with this driverless cable that works on any operating system and all hardware platforms. Deliver uncompressed, high-bandwidth video via the host's native GPU rather than CPU-driven USB video processing, resulting in lower latency, reduced CPU utilization, and more reliable performance, making it ideal for quick installs, conference rooms, and standardized deployments.

Certifications, Reports and Compatibility

Operating System Independent

Applications

• Connect USB-C laptops and tablets to 4K 60Hz HDMI displays in conference rooms, control centers, and workstations

• Deploy a USB-C to HDMI solution in enterprise environments without requiring additional adapters or drivers

Features

• High-Performance Adapter Cable: Connect a USB-C laptop to an HDR-ready 4K 60Hz HDMI display using this 2m active adapter cable that delivers 18Gbps bandwidth, full 4:4:4 / RGB color, 7.1ch audio, and HDCP 2.3 support

• Prevent Costly Cable Disconnects: Maintain stable video links in busy workspaces with a gripping HDMI connector that resists vibration and cable strain, keeping the cable connected to the display in boardrooms, hot desks, and collaboration areas

• Identify HDMI Performance Instantly: Speed up installs with clear markings on the connector that verify the cables capabilities at a glance; Integrated adapter design reduces connection points that cause dropouts, handshakes issues, and field failures

• Deploy Instantly Across Any Platform: Eliminate setup delays with this driverless universal cable that works with all hardware platforms and any OS; Uses the GPU (Intel / AMD / Nvidia) to deliver high-performance graphics with minimal CPU overhead

• The IT Pro's Choice: Our display and video adapters are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and durability; Built to support large-scale deployments, Windows 11 upgrades, and the shift to AI-enabled PCs

General		
	UPC	065030928120
	Warranty	3 Years
Physical & Environmental		
	Color	Black
	Cable OD	0.2 in [4.5 mm]
	Product Length	6.6 ft [2 m]
	Product Width	0.8 in [20.8 mm]
	Product Height	0.4 in [9 mm]
	Weight of Product	4.0 oz [112 g]
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 70C (-4F to 154F)

	Humidity	10% ~ 90% RH
Performance		
	Maximum Data Transfer Rate	18Gbps
	Bandwidth	18Gbps
	Audio Specifications	HDMI - 7.1 Channel Audio
	Maximum Digital Resolutions	3840 x 2160 @ 60Hz
	Video Revision	HDMI 2.0
Hardware		
	4K Support	Yes
	AV Input	USB-C
	AV Output	HDMI
	Audio	Yes
	Connector Plating	Gold
	Cable Jacket Material	TPE (Thermoplastic Elastomer)
	Bus Type	USB-C
	Chipset ID	VL600
Packaging & In-the-Box		
	Included in Package	1 - USB-C to HDMI Cable
	Package Width	4.3 in [11 cm]
	Package Depth	7.5 in [19 cm]
	Package Height	0.9 in [23 mm]
	Shipping (Package) Weight	4.0 oz [112 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-C DP++ (DP Alt-Mode)

Connector 2 (Quantity)	1
Connector 2	HDMI

Product appearance and specifications are subject to change without notice.