

## 3.5in Drive Bay IDE to Single CF SSD Adapter Card Reader

**Product ID:** 35BAYCF2IDE



This Compact Flash IDE adapter is a perfect solution for accessing CompactFlash (CF I, CF II) and IBM Micro Drive media, allowing you to access the flash/micro drive media as if it were an IDE hard drive.

The CF/IDE adapter can be installed in the computer case through simple mounting in an available 3.5in drive bay, for connection to the computer IDE bus through either a 40 or 44-pin connection.

Designed and constructed to provide a reliable media card platform, the CF IDE adapter is backed by StarTech.com's 2-year warranty.

## Certifications, Reports and Compatibility

### Applications

- Use your compact flash card as a bootable and removable device
- Excellent for swapping operating systems quickly without having to take your computer apart.
- Connect your compact flash card to a 40 or 44 pin IDE slot

### Features

- Quick and driver free installation into any IDE 40 pin and 44 pin slot
- Fully compatible with Compact Flash Type I/II and IBM Micro-drive
- Allows Compact flash card to be used as bootable storage

- Easy to use jumpers offer simple master/slave drive setting
- Can be mounted in the front or rear panel of your case, to fit into any 3.5" bay or available expansion slot
- Easily swap cards in and out with built-in push button ejector

---

#### Hardware

Warranty	2 Years
Interface	IDE

---

#### Performance

Maximum Data Transfer Rate	133 MBps
Memory Media Type	CF (Compact Flash I/II Card)

---

#### Connector(s)

Drive Connectors	CompactFlash (50 pin) Slot
Host Connectors	IDE (40 Pin, EIDE/PATA) SP4 (4 pin, Small Drive Power)

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

#### Special Notes / Requirements

Note	This product does not support hot-swapping of flash cards while the PC is powered on. You must turn-off your computer to switch cards.
------	--

---

#### Environmental

Operating Temperature	-55C to 85C (-67F to 185F)
Storage Temperature	-55C to 85C (-67F to 185F)
Humidity	5% ~ 85% RH

---

#### Physical Characteristics

Product Length	3.8 in [97 mm]
Product Width	3.9 in [100 mm]
Product Height	1.0 in [25 mm]



Weight of Product 4.6 oz [129 g]

---

**Packaging Information**

Package Length 8.7 in [22 cm]

Package Width 1.9 in [48 mm]

Package Height 6.2 in [15.8 cm]

Shipping (Package) Weight 7.6 oz [215 g]

---

**What's in the Box**

Included in Package

- Compact Flash to IDE Adapter
- 3.5" Enclosure
- Full Profile Expansion Slot Bracket
- Instruction Manual
- SP4 to LP4 Molex Power Cable

---

***\*Product appearance and specifications are subject to change without notice.***

