

2-Slot USB 3.0 SD Card Reader - SD 4.0, UHS II

Product ID: 2SD4FCRU3



This USB 3.0 SD card reader lets you access two SD cards simultaneously.

You can:

- Download and edit photos and videos
- Back up presentations, documents and spreadsheets
- Distribute content to multiple employees

The card reader transfers files between your USB-A tablet, laptop or desktop computer and the SD card.

The USB SD card reader features SD 4.0 and UHS-II support. It reads and writes to and from the cards at speeds of up to 312MB/s. The reader also supports USB 3.0 connection speeds of up to 5Gbps between the computer and the reader. The reader is backward compatible with USB 2.0 and 1.1.

The dual SD card reader supports all SD cards: SD (Secure Digital), SDHC (Secure Digital High Capacity) and SDXC (Secure Digital Extended Capacity). It also supports UHS cards, and is backward compatible with older SD cards.

The card reader will also support the following card types when connected through an adapter:

- microSD
- miniSD
- MMCmobile
- RS-MMC
- MMCplus

The reader has a small footprint design and comes with a wrap-around USB-A cable. It fits nicely inside a carrying

case. The reader is USB powered, but you can connect a power source to the Micro-USB power port if you require more power.

2SD4FCRU3 is TAA compliant and comes with a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Access multimedia content quickly -- ideal for creative professionals and mobile workers
- Review or edit files on two SD cards simultaneously, out in the field or in the studio

Features

- Save time and access two SD cards simultaneously with this USB 3.0 SD card reader
- Experience fast read/write speeds with USB 3.0 (5Gbps) on each slot
- Perform high-speed file transfers: card reader supports SD 4.0, UHS-II and bus speeds up to 312MB/s
- Edit your photos, videos and presentations anywhere you go with this dual SD card reader

Hardware

| | |
|------------|--|
| Warranty | 2 Years |
| Interface | USB 3.0 |
| Bus Type | USB 3.0 |
| Chipset ID | Genesys Logic - GL3215 Genesys Logic - GL3522 |

Performance

| | |
|----------------------------|---|
| Maximum Data Transfer Rate | 5 Gbps |
| Type and Rate | USB 3.0 - 5 Gbit/s |
| Memory Media Type | SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity) |



| | |
|------------------------|---|
| General Specifications | Supports SD 4.0 and UHS-II (Ultra High Speed) for high speed file transfers, with bus speed up to 312MB/s |
|------------------------|---|

Connector(s)

| | |
|--------------------|-------------------------------------|
| Drive Connectors | SD / MMC Slot |
| Host Connectors | USB Type-A (9 pin) USB 3.0 (5 Gbps) |
| Other Interface(s) | USB Micro-B (5 pin) |

Software

| | |
|------------------|---|
| OS Compatibility | OS independent; No software or drivers required |
|------------------|---|

Special Notes / Requirements

| | |
|-------------------------------|--|
| System and Cable Requirements | Available USB port |
| Note | USB powered. For additional power, connect the USB cable on your power source to the AUX Micro-B power port. |

Power

| | |
|----------------|---|
| Power Source | Not Included (not required for standard applications) |
| Output Voltage | 5 DC |
| Output Current | 2000 mA |
| Plug Type | USB Micro-B |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 70C (-4F to 158F) |
| Humidity | 5% ~ 90% |

Physical Characteristics

| | |
|----------------|------------------|
| Color | Black |
| Material | Plastic |
| Cable Length | 5.0 in [12.7 cm] |
| Product Length | 4.2 in [10.6 cm] |
| Product Width | 2.7 in [69.5 mm] |



Product Height 0.5 in [13.5 mm]

Weight of Product 2.0 oz [57.0 g]

Packaging Information

Package Length 6.9 in [17.4 cm]

Package Width 5.7 in [14.4 cm]

Package Height 1.3 in [32.0 mm]

Shipping (Package) Weight 5.0 oz [142.0 g]

What's in the Box

Included in Package dual-slot SD card reader

quick-start guide

****Product appearance and specifications are subject to change without notice.***

