4 Port VGA Video Splitter - Wall Mountable

Product ID: ST124WEU

The ST124WEU 4 Port wall-mountable VGA Video Splitter offers outstanding quality and distance, allowing you to deliver high resolution VGA video from a single video source to up to four monitors simultaneously.

Supporting a maximum VGA video bandwidth of up to 250MHz and resolutions up to 1600 x 1200, the device is sure to deliver on image quality. The wall-mountable multi-display VGA video splitter is very simple to install, allowing you to locate screens up to 65m (210ft) away from the VGA video source.

The video splitter provides versatile installation options, with top-side connection ports the unit can lay flat on or under your workspace , or you have the option to mount the splitter on a wall making it easy to position the VGA splitter as needed. A scalable video splitting solution, the device also allows you to cascade the signal using two additional splitters for broadcast from a single VGA source to up to 64 VGA monitors.

Typical applications of this product would include digital signage, retail and tradeshow environments, educational and government facilities, or corporate displays where high quality multi-monitor VGA video is required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Use for in-store product merchandising in retail environments to give your advertisements greater visibility

• Display travel schedules and alerts in airports, bus terminals and train stations

• Create engaging multimedia presentations for demonstration in lecture halls and classrooms

• Get your message across multiple displays for trade-shows or information booths/kiosks

• Quick and easy solution to split a video signal in an auditorium or house of worship

Features

• Compact design with convenient topside connection

• Lays flat or mounts on the wall

• Supports resolutions up to 1600 x 1200

• Supports cable distances up to 65m / 210ft

• 250MHz video bandwidth

• Supports Cascading up to 3 levels

Hardware		
	Warranty	2 Years
	AV Input	VGA
	Ports	4
	AV Output	VGA
	Audio	No
Performance		
	Maximum Cable Length	213.2 ft [65 m]
	Maximum Analog Resolutions	1600x1200
	Bandwidth	250 MHz
Connector(s)		
	Connector A	1 - VGA (15 pin, High Density D-Sub)
	Connector B	4 - VGA (15 pin, High Density D-Sub)
Power		
	Power Source	AC Adapter Included

	Input Voltage	230 AC
	Output Voltage	9V DC
	Output Current	0.3A
	Center Tip Polarity	Positive
Environmental		
	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	-20C to 60C (-4F to 140F)
Physical Characteristics		
	Color	Silver
	Material	Plastic
	Product Length	4.1 in [10.5 cm]
	Product Width	3.2 in [8.2 cm]
	Product Height	1.1 in [2.8 cm]
	Weight of Product	4.6 oz [129 g]
Packaging Information		
	Package Quantity	1
	Package Length	9.4 in [24 cm]
	Package Width	2.3 in [59 mm]
	Package Height	6.4 in [16.2 cm]
	Shipping (Package) Weight	1.1 lb [0.5 kg]
What's in the Box		
	Included in Package	1 - 4 Port VGA Splitter
		1 - Power Adapter
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.