

## USB 3.0 Front Panel 4 Port Hub – 3.5in or 5.25in Bay

**Product ID:** 35BAYUSB3S4



The 35BAYUSB3S4 3.5-inch Front Bay to 4-Port USB 3.0 Panel Hub is TAA compliant and turns any available 3.5-inch computer case front bay into a 4-Port USB 3.0 hub.

Using only a single USB connection, this front panel hub adds four easily accessible USB ports to the front of your computer case through a 3.5-inch bay, or through a 5.25-inch bay using the optional Front Bay Bracket Adapter (BRACKETFDBK) accessory. Each of the added ports is compliant with the USB 3.0 standard which supports up to 5 Gbps of bandwidth (10x faster than the USB 2.0 standard) and up to 900mA of power.

Accessorize with the PEXUSB3S11 PCI Express card to provide an internal USB 3.0 port, so as to keep the external ports free for external devices. Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Expand your system's USB 3.0 capabilities with additional ports for connecting high speed external storage devices
- Add easier to access USB ports to the front of a computer system instead of the rear
- Make use of an internal USB port and unused 3.5" front bay to increase the system's expandability

### Features

- Four front accessible USB type-A ports
- SuperSpeed USB 3.0 compliant, supporting data transfer rates up to 5 Gbps

- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Fits into any 3.5" computer case front bay
- Provides up to 900mA of power per port
- USB Link LED indicator for each port
- TAA Compliant

---

#### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	4
Interface	USB 3.0
Bus Type	USB 3.0
	USB 3.0
Chipset ID	VIA/VLI - VL811+

---

#### Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

#### Connector(s)

Internal Ports	USB Type-B (9 pin) USB 3.0 SATA Power (15 pin)
External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

#### Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

---

#### Special Notes / Requirements

System and Cable Requirements	Available 3.5 inch front bay
	Available USB 3.0 type A port



---

**Indicators**

LED Indicators	USB Device Link (Green)
----------------	-------------------------

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	5C to 50C (41F to 122F)
Storage Temperature	-25C to 70C (-13F to 158F)
Humidity	20% ~ 80% RH

---

**Physical Characteristics**

Color	Black
Form Factor	Drive Bay
Material	Plastic
Product Length	4.7 in [12 cm]
Product Width	3.9 in [100 mm]
Product Height	1.0 in [25 mm]
Weight of Product	3.5 oz [98 g]

---

**Packaging Information**

Package Length	5.7 in [14.5 cm]
Package Width	6.9 in [17.5 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	7.3 oz [208 g]

---

**What's in the Box**

Included in Package	Instruction Manual
	3.5" Front Panel
	Mounting Screw Kit



USB 3.0 Cable

---

***\*Product appearance and specifications are subject to change without notice.***

