3U Steel Lockable 19in Rackmount Drawer for AV, Network, Server Cabinets, 22lb (10kg) Capacity, Rear Cable Pass-through Holes, Keys Included

Product ID: 3U-RACK-MOUNT-DRAWER



Keep essential tools and equipment securely stored inside a standard 19-inch rack with this lockable 3U rackmount drawer.

Store test equipment, spare components, accessories, and essential supplies directly inside the rack. The slide-out design keeps frequently used items organized and accessible during maintenance, repairs, and system modifications.

An integrated lock helps restrict access to valuable or mission-critical equipment. The durable steel construction protects stored items and keeps them securely contained within the rack cabinet.

Three rear cable-access holes support power or data connections to equipment stored inside the drawer. This helps reduce cable clutter and keeps connected devices neatly integrated into the rack setup.

The 3U drawer fits standard 19-inch cabinets and supports up to 22lb (10kg). Its rackmount design adds dedicated storage alongside servers, AV equipment, and other rack-mounted hardware without requiring separate shelving.

Certifications, Reports and Compatibility

Applications

• Keep test equipment, adapters, control accessories, remotes, and other AV essentials protected and within reach during installation and troubleshooting.

• Organize console cables, transceivers, diagnostic tools, cleaners, and critical spares inside the data center rack for

quick access during maintenance and repairs.

Features

• Keep Critical Gear Close at Hand: 3U rackmount drawer provides dedicated storage for valuable service equipment, accessories, and essential supplies, helping technicians stay organized and respond faster during maintenance or repairs

• Organize Cable Connections: Three rear cable-access holes provide a path for power or data cables when connections to stored equipment are required, helping reduce cable clutter and maintain a cleaner rack installation

• Restrict Unauthorized Access: Integrated lock limits access to valuable service equipment and supplies, while the steel enclosure keeps stored items secure and protects them in busy data center and AV environments

• Organize Standard Rack Cabinets: Slide-out drawer (13.2-inch / 33.7cm internal depth) supports up to 22lb (10kg) and fits 19" racks or cabinets, giving IT and AV professionals durable storage that integrates neatly alongside other rack-mounted hardware

• The IT Pro’s Choice: Engineered and tested for professional rack installations, this lockable steel drawer provides dependable equipment storage backed by free lifetime 24/5 multilingual technical assistance

General		
	UPC	065030905121
	Warranty	5 Years
Physical & Environmental		
	Color	Black
	Materials	Steel
	Product Length	14.1 in [35.7 cm]
	Product Width	19.0 in [48.3 cm]
	Product Height	5.2 in [13.2 cm]
	Weight of Product	13.7 lb [6.2 kg]
	Minimum Mounting Depth	0.0 in [0 mm]
Performance		
	Weight Capacity of Work Surface	22.1 lb [10 kg]
Hardware		
	Wallmountable	No

	U Height	3U
	Cable Management	Yes
	Tools Included	No
	Mounting Options	Front Mount (Front Only)
Packaging & In-the-Box		
	Included in Package	1 - Rack-Mount Drawer
		2 - Keys
		4 - Plastic Washers
		4 - M6 Cage Nuts
		4 - M6 Mounting Screws
		1 - Product Documentation
	Package Width	15.4 in [39 cm]
	Package Depth	19.7 in [50 cm]
	Package Height	6.7 in [17 cm]
	Shipping (Package) Weight	15.9 lb [7.2 kg]

Product appearance and specifications are subject to change without notice.