10m USB 3.0 (5Gbps) Active Extension Cable - M/F

**Product ID:** USB3AAEXT10M

The USB3AAEXT10M, 10-meter Active USB 3.2 Gen 1 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 3.2 Gen 1 devices of up to 10-meters (32.8-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations; the active USB 3.2 Gen 1 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Up to 2 of these cables can be daisy-chained together, allowing the connection to be extended a total of 20-meters. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter provided with the cable.

The USB3AAEXT10M extension cable (USB Extender) supports high speed USB 3.2 Gen 1 transfer rates of up to 5Gbps, and is backed by StarTech.com's 2-year Warranty.

## Certifications, Reports and Compatibility

## Applications

• Extend the distance of USB peripherals beyond the USB 3.0 3-meter limitation

• Cascade up to 2 levels

• Backwards compatible with USB 2.0/1.1 devices

## Features

• Fully shielded for error-free connections

• Plug-and-play, no driver required

• USB bus-powered

• Universal external power source also included

• Blue LED indicator x1 for Extension Cable and USB port connection status monitoring

• OS Independent

| | | |
|---|---|---|
| **Hardware** | | |
| | Warranty | 2 Years |
| | Connector Plating | Nickel |
| | Cable Jacket Material | PVC - Polyvinyl Chloride |
| **Connector(s)** | | |
| | Connector A | 1 - USB Type-A (9 pin, 5 Gbps) |
| | Connector B | 1 - USB Type-A (9 pin, 5 Gbps) |
| **Special Notes / Requirements** | | |
| | Note | Cascade up to 2 USB3AAEXT10M devices together for further extension |
| **Power** | | |
| | Power Source | AC Adapter Included |
| | Input Voltage | 100 - 240 AC |
| | Input Current | 0.35 A |
| | Output Voltage | 5 DC |
| | Output Current | 2A |
| | Center Tip Polarity | Positive |

| | | |
|---|---|---|
| | Plug Type | H |
| | Power Consumption (In Watts) | 10 |
| **Physical Characteristics** | | |
| | Color | Black |
| | Cable Length | 32.8 ft [10 m] |
| | Product Length | 32.8 ft [10.0 m] |
| | Product Width | 0.8 in [2.0 cm] |
| | Product Height | 0.4 in [1.0 cm] |
| | Weight of Product | 17.3 oz [491.0 g] |
| **Packaging Information** | | |
| | Package Quantity | 1 |
| | Package Length | 8.9 in [22.6 cm] |
| | Package Width | 8.4 in [21.4 cm] |
| | Package Height | 2.4 in [60.0 mm] |
| | Shipping (Package) Weight | 26.8 oz [758.0 g] |
| **What's in the Box** | | |
| | Included in Package | 1 - 10 m USB 3.0 Active Extension Cable - M/F |
| | | 1 - Universal Power Adapter |
| | | 1 - Plug Adapters for North America, UK, Europe, and Australia |

***Product appearance and specifications are subject to change without notice.***