6 ft Black SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

Produkt ID: USB3SAB6BK

StarTech.com's 6ft Black SuperSpeed USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 6ft USB 3.2 Gen 1 cable offers a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifikat, rapporter och kompatibilitet

Användning

• Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

Funktioner

- Designed and constructed to SuperSpeed USB 3.2 Gen1 Specifications
- Molded connectors with strain relief

Hårdvara		
	Garantipolicy	Lifetime
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kabelskärmning	Folieskärmad partvinnad
Prestanda		
	Typ och hastighet	USB 3.0 - 5 Gbit/s
Kontakt(er)		
	Connector A	1 - USB Type-A (9-stifts) USB 3.0 (5 Gbps)
	Connector B	1 - USB 3.2 Type-B (9 stift, Gen 1, 5 Gbps)
Miljö		
	Drifttemperatur	-10°C to 50°C (14°F to 122°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	0~75% RH
Utseende		
	Färg	Svart
	Tråddimension	28 AWG
	Kabellängd	6.0 ft [1.8 m]
	Produktlängd	6.0 ft [1.8 m]
	Produktbredd	0.5 in [1.4 cm]
	Produkthöjd	0.5 in [1.2 cm]
	Produktvikt	2.9 oz [82.2 g]
Förpackning		
	Förpackningsantal	1

	Package Length	0.0 in [0.1 mm]
	Package Width	4.9 in [12.5 cm]
	Package Height	8.9 in [22.5 cm]
	Fraktvikt (förpackning)	3.1 oz [87.2 g]

Vad det är i lådan		
	Ingår i paketet	1 - 6ft black USB 3.0 A to B cablecable

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.