3 ft SuperSpeed USB 3.0 (5Gbps) Cable A to Micro B

Product ID: USB3SAUB3

The USB3SAUB3 3-foot SuperSpeed USB 3.2 Gen 1 Cable (A to Micro B) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the USB 3.2 Gen 1 A to Micro B cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication to provide a quick and easy way to connect to an external storage solution with astounding throughputs of up to 5Gbps (when used with a USB 3.2 Gen 1 host and device).

The 3-foot USB 3.2 Gen 1 A to Micro B cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• Connecting Micro USB 3.0 devices to a SuperSpeed USB 3.0 compatible PC or Laptop

Features

• Shielded Twisted Pair (STP) design, helping to eliminate electro-magnetic interference (EMI)

• Data transfer rates up to 5Gbps

- Backwards compatible with USB 2.0
- Molded connectors with strain relief

Hardware		
	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance		
	Type and Rate	USB 3.0 - 5 Gbit/s
Connector(s)		
	Connector A	1 - USB Type-A (9 pin, 5 Gbps)
	Connector B	1 - USB 3.0 Micro-B (10 pin, SuperSpeed)
Physical Characteristics		
	Color	Blue
	Wire Gauge	28 AWG
	Cable Length	3.0 ft [0.9 m]
	Product Length	3.0 ft [0.9 m]
	Weight of Product	1.5 oz [43 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Package Height	0.4 in [9 mm]
	Shipping (Package) Weight	1.8 oz [52 g]
What's in the Box		
	Included in Package	1 - 3 ft SuperSpeed USB 3.0 Cable A to Micro B

Product appearance and specifications are subject to change without notice.