4 Port USB A Female Slot Plate Adapter

**Product ID:** USBPLATE4

The USBPLATE4 4 port USB 2.0 slot plate adapter converts the USB pins on your motherboard into four USB-A female ports, enabling you to add USB connections to the back of your PC.

Backed by Lifetime Warranty, the USBPLATE4 is designed and constructed for maximum durability, to ensure dependable performance.

Please Note: Check your motherboard's manual for the USB pinout diagram. The USBPLATE wiring scheme is: Red=Power, Green=Signal, White=Signal, Black=Ground

## Certifications, Reports and Compatibility

## Applications

• Mount four USB-A female ports to the back of your PC by connecting them to 2x 4 or 5 pin IDC motherboard connections

## Features

• 4x USB-A female ports

• 2x IDC 10-pin Female connectors

• Supports 4 or 5 pin motherboard connections

• Separate cables supports 2 rows of 4/5

| | | |
|---|---|---|
| **Performance** | | |
| | Warranty | Lifetime |
| | Type and Rate | USB 2.0 - 480 Mbit/s |
| **Connector(s)** | | |
| | Connector A | 2 - IDC (10 pin, Motherboard Header) |
| | Connector B | 4 - USB 2.0 Type-A (4 pin, 480Mbps) |
| **Environmental** | | |
| | Operating Temperature | -5C to 40C (41F to 104F) |
| | Storage Temperature | -5C to 80C (41F to 176F) |
| | Humidity | 20%~60% |
| **Physical Characteristics** | | |
| | Color | Gray |
| | Cable Length | 11.3 in [286 mm] |
| | Product Length | 11.3 in [28.6 cm] |
| | Product Width | 0.8 in [2.1 cm] |
| | Product Height | 4.7 in [12.0 cm] |
| | Weight of Product | 2.4 oz [68.0 g] |
| **Packaging Information** | | |
| | Package Quantity | 1 |
| | Package Length | 8.9 in [22.5 cm] |
| | Package Width | 4.9 in [12.5 cm] |
| | Package Height | 0.9 in [2.2 cm] |
| | Shipping (Package) Weight | 2.6 oz [73.0 g] |

**What's in the Box**

| | |
|---|---|
| Included in Package | 1 - 4 Port USB 2.0 Connector Backplate |

***Product appearance and specifications are subject to change without notice.***