6in Micro USB Cable - A to Micro B

Product ID: UUSBHAUB6IN

The UUSBHAUB6IN 6-inch USB A to Micro-B cable provides a high quality connection between Micro USB-equipped USB 2.0 mobile devices (such as BlackBerry or Android-based smart phones, digital cameras, PDAs, Tablet PC devices and GPS systems) and a USB-capable computer, for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• An ideal replacement cable for connecting mobile devices to a USB capable computer

Features

• 1x USB 'A' male connector

• 1x USB Micro 'B' male connector

• Offers 6” in cable length

• Aluminum-Mylar Foil with Braided Shielding

• Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware		
	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride
Performance		
	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)		
	Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	Connector B	1 - USB Micro-B (5 pin)
Environmental		
	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-10C to 30C (14F to 86F)
	Humidity	30%-75% RH
Physical Characteristics		
	Color	Black
	Wire Gauge	24/30 AWG
	Cable Length	6.0 in [152 mm]
	Product Length	6.0 in [15.2 cm]
	Product Width	0.6 in [1.5 cm]
	Product Height	0.3 in [0.8 cm]
	Weight of Product	0.4 oz [10.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]

Package Height	0.3 in [8.0 mm]
Shipping (Package) Weight	0.6 oz [16.0 g]

What's in the Box

Included in Package	1 - 6in Micro USB Cable - A to Micro B

Product appearance and specifications are subject to change without notice.