

Replacement HDMI Transmitter for 4KHDMI-WIRELESS-65FT, 65ft Range, 4K 60Hz, USB Powered, Plug and Play

Product ID: 4KHDMI-WIRELESS-TX




Restore wireless AV fast by adding a standalone HDMI transmitter to your IT closet that pairs with your existing HDMI receiver, no full kit replacement required.

Replace missing or failed transmitters instead of entire kits to reduce costs and downtime. Keep a spare transmitter in inventory and get meeting rooms, classrooms, or event spaces back online in minutes when a transmitter goes missing, avoiding delays and emergency reorders.

One-button pairing works with your current 4KHDMI-WIRELESS-65FT receivers, no apps, drivers, or network changes. IT can re-establish links quickly across rooms, reducing troubleshooting time and keeping presentations uninterrupted.

Compact, USB-powered units install instantly so non-technical users can connect and present without cables or training, lowering support tickets across huddle spaces and trade shows.

Certifications, Reports and Compatibility



Applications

- Replace missing or failed transmitters instead of entire kits to reduce costs and downtime
- Keep a spare transmitter in inventory and get meeting rooms, classrooms, or event spaces back online in minutes when a transmitter goes missing

Features

- **Restore Wireless AV Without Full System Replacement**: Add a standalone transmitter to your IT inventory to quickly recover wireless HDMI, avoiding full kit replacement and reducing meeting room downtime caused by missing transmitters
- **Easy Pairing Across Existing Receivers**: Enable one-button pairing with current wireless HDMI receivers, removing software, drivers, and network dependencies to simplify setup and keep AV systems operational with minimal IT effort
- **Deploy with Zero Training Required**: Compact, plug-and-play design allows non-technical users to install and present instantly in meeting rooms, huddle spaces, and trade shows, eliminating cable runs, reducing setup time, and avoiding support tickets
- **USB-Powered Transmitter and Receiver for Flexible Deployment**: Both units require USB power via included cables, with no external power bricks needed; Power from displays, laptops, or USB chargers to enable flexible placement and streamlined installations
- **The IT Pro's Choice**: Backed by decades of connectivity expertise from legacy VGA to modern USB4 and AVoIP solutions; Work with a single trusted partner for all your A/V connectivity needs; Free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Ports	1
Audio	Yes
Rack-Mountable	No
Chipset ID	Transmitter: VCT6601
Daisy-Chain	No

Performance

Max Distance	66ft [20m]
Frequency	5GHz

Connector(s)

Local Unit Connectors	1 - HDMI
-----------------------	----------

Software

OS Compatibility No Drivers or Software Required

Special Notes / Requirements

Note Transmission distances may vary based on the installation environment.

Solid structures like walls, bricks, and glass can reduce or completely block signals.

Indicators

LED Indicators 1 - Power LED:
Solid Red - The device is receiving power

1 - Signal LED:
Solid - The unit is successfully connected
Slow Flash - Waiting for connection
Quick Flash - The unit is in pairing mode

1 - Video LED:
Off - No input video signal detected
Solid - Video input signal detected
Quick Flash - Restoring to factory defaults

Power

Power Source USB-Powered

Power Consumption (In Watts) < 4.5W

Environmental

Operating Temperature -20C to 50C (-4F to 122F)

Storage Temperature -30C to 70C (-22F to 158F)

Humidity 0% ~ 90% RH

Physical Characteristics

Color Space Gray

Material ABS

Cable Length	4.7 in [12 cm]
Product Length	9.1 in [230 mm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [15 mm]
Weight of Product	2.0 oz [58 g]

Packaging Information

Package Length	5.9 in [14.9 cm]
Package Width	7.8 in [19.9 cm]
Package Height	3.1 in [8.0 cm]
Shipping (Package) Weight	12.0 oz [340.0 g]

What's in the Box

Included in Package	1 - HDMI Transmitter
	1 - Product Documentation

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***