

Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/LC - 1 m

Produkt ID: 50FIBLCLC1



The 50FIBLCLC1 1m LSZH LC to LC Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Funktioner

- Immune to electrical interference
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

Hårdvara

Garantipolicy	Lifetime
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberstorlek	50/125

Prestanda

Maximal dataöverföringshastighet	10Gbps
Kabelklassificering	1Gbps / 10Gbps
Fiberklassificering	OM2
Fibertyp	Multiläge

Kontakt(er)

Connector A	Fiberoptisk LC duplex
Connector B	Fiberoptisk LC duplex

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~90% RH

Utseende

Färg	Orange
Kabellängd	39.4 in [100 cm]



Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	0.7 oz [19.0 g]

Förpackning

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.5 in [12.0 mm]
Fraktvikt (förpackning)	1.0 oz [28.0 g]

Vad det är i lådan

Ingår i paketet	1m Multimode 50/125 Duplex Fiber Patch Cable LC - LC
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

