


5m Fiber Optic Cable - Multimode Duplex 50/125 - LSZH Fiber Jumper Cord - LC/SC

Produkt ID: 50FIBLCSC5



The 50FIBLCSC5 5m LSZH LC to SC Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems

- Ideal solution for data applications requiring high speed data transmission

Funktioner

- Immune to electrical interference
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

Hårdvara

Garantipolicy	Lifetime
Fiberstorlek	50/125
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberklassificering	OM2

Prestanda

Maximal dataöverföringshastighet	10Gbps
Kabelklassificering	1Gbps / 10Gbps
Fibertyp	Multiläge

Kontakt(er)

Connector A	1 - Fiberoptisk LC duplex
Connector B	1 - Fiberoptisk SC duplex

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~90% RH

Utseende

Färg	Orange
Kabellängd	16.4 ft [5 m]
Produktlängd	16.4 ft [5.0 m]
Produktbredd	0.0 in [0.0 cm]
Produkthöjd	0.0 in [0.0 cm]
Produktvikt	2.9 oz [83.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	8.7 in [22.0 cm]
Paketets bredd	7.9 in [20.0 cm]
Paketets höjd	1.1 in [2.7 cm]
Fraktvikt (förpackning)	3.2 oz [92.0 g]

Vad det är i lådan

Ingår i paketet	1 - 5m Multimode 50/125 Duplex Fiber Patch Cable LC - SC
-----------------	--

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.