

Ultra-Slim Articulating TV Wall Mount for up to 65-inch and 99lb/45kg Flat Screens, VESA 600x400, TAA-Compliant Low-Profile Bracket

Product ID: 65SAP2-TV-WALL-MOUNT



Create a TV mounting solution with this articulating wall mount that supports up to 65-inch televisions and 99lb (45kg). Use in conference rooms, customer-facing applications, and collaborative spaces where durability, precision, and presentation matter.

Mount sits just 1.5in (4cm) from the wall for a sleek, unobtrusive look and extends to a maximum of 23.6in (60cm) when needed. For perfect screen positioning, you can tilt (+2/-12), swivel (+/-60), and rotate (+/-2) the display. The dual articulating arms and wider wall plate (16in North America spacing) provide smooth motion and stability during adjustments.

This VESA-compatible wall mount supports patterns up to 600x400mm and includes hardware, spacers, and a wall template for clean installation. It secures to wood studs, brick, or concrete surfaces, offering flexibility across environments. Integrated cable channels keep wires organized, while the silver steel and aluminum frame with decorative covers creates a refined, professional look from any angle.

Certifications, Reports and Compatibility



Applications

- Mount flat-screen TVs in conference rooms where a sleek, low-profile design enhances professional presentation spaces
- Ideal choice for executive offices for a clean and modern look

- Optimize small areas by keeping the display close to the wall without sacrificing wall clearance

Features

- **Securely Install Large Displays**: Articulating wall mount supports up to 65-inch and 99lb (45kg) TV screens, making it ideal for meeting rooms, AV walls, and digital signage; VESA compatible up to 600x400mm for broad display support
- **Create a Clean, Ultra-Low-Profile Look**: Slim TV mount collapses to just 1.5in (4cm) from the wall for a clean professional aesthetic; Extends up to 23.6in (60 cm) for easy rear access and flexible positioning
- **Fine-Tune Viewing Angles**: Tilt +2/ -12, swivel 60, and rotate 2 for effortless post-install adjustments and perfect leveling; Dual articulating arms ensure smooth, stable motion
- **Supports Multiple Wall Types**: TV bracket includes wall template, screws, anchors, spacers, and tools for mounting on wood studs (16in spacing), brick, or concrete; Built-in cable management keeps customer-facing setups tidy
- **The IT Pro's Choice**: Our TV wall mounts are tested in our Innovation Lab for reliable, long-lasting performance and stability in professional environments, from conference rooms to digital signage; Backed by free lifetime 24/5 multilingual assistance

Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	Yes
Tools Included	Yes
Articulating	No
# of Displays Supported	1
Orientation	Horizontal
Mounting Options	Wall-Mount
Minimum Profile from Wall	1.6 in [40 mm]
VESA Hole Pattern(s)	200x100 mm 200x200 mm 200x300 mm 200x400 mm

300x200 mm

300x300 mm

400x200 mm

400x300 mm

400x400 mm

500x300 mm

600x300 mm

600x400 mm

Performance

General Specifications	Minimum Distance to Wall: 1.5in (4cm)
	Maximum Distance to Wall: 23.6in (60cm)
Weight Capacity (Per Display)	99.2 lb [45 kg]
Minimum Display Size	32"
Maximum Display Size	65"
Fits Curved Display	No
Fits UltraWide Displays	No
Video Wall	No
Height Adjustment	No
Display Tilt	+2 / -12
Swivel / Pivot	+60 / -60
Display Rotation	+2 / -2
Anti-theft	No

Physical Characteristics

Color	Black & Silver
Construction Material	Aluminum and Steel

Product Length	28.7 in [730 mm]
Product Width	18.9 in [480 mm]
Product Height	1.6 in [40 mm]
Weight of Product	16.0 lb [7.3 kg]

Packaging Information

Package Length	17.9 in [45.4 cm]
Package Width	31.5 in [79.9 cm]
Package Height	2.4 in [6.1 cm]
Shipping (Package) Weight	21.1 lb [9.6 kg]

What's in the Box

Included in Package	1 - TV Wall Mount Assembly
	2 - VESA Vertical Brackets
	2 - VESA Vertical Bracket Screws
	1 - 5mm Hex Key
	1 - 10mm Wrench
	4 - M4x12mm Screws
	4 - M4x18mm Screws
	4 - M5x12mm Screws
	4 - M6x12mm Screws
	4 - M6x18mm Screws
	4 - M8x12mm Screws
	4 - M8x18mm Screws
	4 - M8x25mm Screws
	5 - Wall Mounting Screws
	5 - Concrete Anchors

4 - Washers

1 - Wall Mounting Template

1 - Product Documentation

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

