

7-Port USB Hub - USB 3.0 5Gbps - USB-A to 7x USB-A - Compact Self Powered USB-A Hub w/
35W Power Supply - Desktop/Laptop USB Hub - USB Expansion Hub

Product ID: 5G7AS-USB-A-HUB



This 7-Port USB 3.2 Gen 1 (5Gbps) hub adds seven USB Type-A ports to a computer, with the added benefit of a dedicated on/off switch. The USB hub is self-powered with an included power adapter, making it ideal for a fixed workstation setup.

The USB 3.2 Gen 1 hub expands your laptop or desktop computer's USB connectivity, adding seven USB ports. It is backward compatible with USB 2.0, ensuring support for a wide range of USB devices such as thumb drives, HDDs/SSDs, mice, keyboards, webcams and USB headsets.

The USB hub is self-powered, using an included power adapter. It includes one fast-charge port that supports BC 1.2, providing 1.5A (7.5W) of power. It also supports CDP (Charging Downstream Port) applications.

The 7-Port USB Hub is OS independent, supporting all operating systems (Windows, macOS, ChromeOS, iPadOS and Android), and installs automatically when connected to a computer.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that is compatible with a wide variety of IT connectivity accessories. The applicable software for this product is the USB Event Monitoring Utility. Use this utility to track and log connected USB devices.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/connectivity-tools

This product is backed for 2-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Connect external storage devices (thumb drives, HDDs/SSDs), HD cameras, mice, keyboards, webcams, and USB headsets to a computer

Features

- **7-PORT USB HUB:** Self-powered (adapter incl) USB 3.2 Gen 1 (5Gbps) expansion hub w/USB-A host, 7x USB-A ports; 3.3ft (1m) detachable host cable; 1x BC 1.2 charging up to 1.5A/7.5W, 35W of power dynamically shared between 7 ports; Dedicated on/off switch
- **FAST CHARGE PORT WITH BC 1.2:** The 7 port USB-A hub includes a fast charge port that provides power up to 1.5A (7.5W); 35W max power is shared across all used ports and connected devices; Features a Charging Downstream Port (CDP) for data and charging
- **IT PRO PERFORMANCE:** Overcurrent Protection protects connected peripherals from overdrawing power, reducing potential of device dropout/laptop shut down, Wake On USB wakes your laptop from a sleep state, USB Event Monitoring tracks/logs connected devices
- **COMPATIBILITY:** OS independent; Supports all operating systems, including Windows, Linux, ChromeOS; Compatible with USB Type-A host devices such as Lenovo X1 Carbon, Dell XPS, Microsoft Surface; Works w/USB 2.0 devices
- **Our Advantage:** Includes IT Pro Connectivity Tools software to improve USB security on Windows systems - Featuring USB Event logging functionality with timestamps to allow admins to identify potentially malicious devices

Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	Yes
Ports	7
Interface	USB 3.2 Gen 1 (5Gbps)
Industry Standards	USB 3.2 Gen 1 - Backward compatible with USB 2.0 and 1.1

Chipset ID VIA VL817

Performance

Total USB Power Output	35W
Maximum Data Transfer Rate	5 Gbps (USB 3.2 Gen 1)
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
UASP Support	Yes
Supported Charging Modes	Charging Downstream Port (CDP)
MTBF	50,000 Hours

Connector(s)

External Ports	7 - USB Type-A (9 pin, 5 Gbps)
Host Connectors	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

Note	USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps), USB 3.0 (5Gbps) and SuperSpeed USB.
------	---

Indicators

LED Indicators	1 - Power (Solid Green)
----------------	-------------------------

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	1.2A
Output Voltage	5 DC
Output Current	7A
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	5C to 50C (41F to 122F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	10~90% RH

Physical Characteristics

Color	Black
Form Factor	Compact
Material	Plastic
Cable Length	3.3 ft [1 m]
Product Length	3.7 in [9.3 cm]
Product Width	2.4 in [6.0 cm]
Product Height	0.9 in [2.2 cm]
Weight of Product	2.9 oz [81.0 g]

Packaging Information

Package Quantity	1
Package Length	7.6 in [19.2 cm]
Package Width	11.4 in [29.0 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	11.3 oz [320.0 g]

What's in the Box

Included in Package	1 - USB Hub
	1 - 3.3ft (1m) USB 3.0 Cable
	1 - Power Adapter

**Product appearance and specifications are subject to change without notice.*