

6ft (1.8m) Heavy Duty PDU Power Cord, C14 to C15, 15A 250V, 14AWG, Green PDU Power Cable, C14 to C15 Heavy Gauge AC Power Cord, TAA Compliant, UL Listed

**Product ID:** 8915-4606-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Heavy Duty power cord supports high-powered equipment and PDUs

## Features

- **HEAVY DUTY POWER CORD:** 6ft (1.8m) 14AWG Green Heavy Duty PDU power cord with IEC 60320 C14 to IEC 60320 C15 connector is suitable for servers or high-powered equipment; Indoor use; Rated to carry 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C15; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Green; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C15 connector works with most servers, switches, and high-power rackmount appliances; Replacement PDU power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C15 Power

---

### Power

Input Voltage	250V AC
Input Current	15A

Output Current	15A
----------------	-----

---

**Environmental**

Operating Temperature	-20 to 105C (-4 to 221F)
-----------------------	--------------------------

Storage Temperature	-20 to 105C (-4 to 221F)
---------------------	--------------------------

Humidity	0% to 65% RH
----------	--------------

---

**Physical Characteristics**

Color	Green
-------	-------

Wire Gauge	14 AWG
------------	--------

Cable Length	6.0 ft [1.8 m]
--------------	----------------

Cable OD	0.3 in [7.8 mm]
----------	-----------------

Product Length	6.0 ft [1.8 m]
----------------	----------------

Product Width	1.1 in [2.9 cm]
---------------	-----------------

Product Height	0.8 in [2.1 cm]
----------------	-----------------

Weight of Product	0.0 oz [0.0 g]
-------------------	----------------

---

**Packaging Information**

Package Length	5.7 in [14.5 cm]
----------------	------------------

Package Width	11.4 in [29.0 cm]
---------------	-------------------

Package Height	0.9 in [2.4 cm]
----------------	-----------------

Shipping (Package) Weight	10.8 oz [306.0 g]
---------------------------	-------------------

---

**What's in the Box**

Included in Package	1 - 6ft C14 to C15 Heavy-Duty Power Extension Cord - Green
---------------------	--

---

*\*Product appearance and specifications are subject to change without notice.*