

Mobile Projector and Laptop Stand/Cart - Heavy Duty Portable Projector Stand (2 Shelves, hold 22lb/10kg each) - Height Adjustable Rolling Presentation Cart w/Lockable Wheels

Product ID: ADJPROJCART



This all-steel projector and laptop stand enables you to setup a mobile multimedia workstation that you can easily move between classrooms, boardrooms, and conference rooms. It has two device platforms that each support 22lb (10kg). This rolling cart is equipped with durable casters (2 lockable) that provide ease of transportation.

With the two integrated device trays, this mobile projector trolley adjusts to your needs letting you choose where to mount your projector, laptop, and other media devices. Both trays have safety ledges that help prevent your equipment from sliding.


The upper tray has surface area of 13.8"x11.8" and lets you setup a laptop or projector depending on your needs. You can adjust its height (37.4" to 57" from the floor) and tilting angle (+/-12) to provide a better viewing experience that will adjust to your presentation needs. Adjustments can be made by hand via the rotary knob locks.

The lower tray has a surface of 14.4"x11.8" and it sits at 27" from the floor.

With a base area of 17.9"x19.7", this AV projector will comfortably support a combined load of 20 kg. For added security, you can keep your devices in place by running straps through the thin openings of the top and bottom trays (straps not included). Additionally, this cart comes with 2 cable management clips that will let you run your cables through the pole in a tidy and safe manner; and help with the transportation of your setup.

ADJPROJCART is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a presentation workstation with versatile applications in schools, business settings, corporate, and institutional environments.
- Add flexibility to the classroom or work environment with mobile presentation solution

Features

- **MOBILE PROJECTOR AND LAPTOP STAND:** This heavy-duty mobile cart provides 2 shelves (at different heights) that each support 22lb (10kg); Durable rolling projector cart has a strong/sturdy base (17.9" x 19.7"/45.5cm x 50.2cm) with lockable casters/wheels
- **HEIGHT ADJUSTABLE TOP TRAY:** Ventilated top shelf with a surface of 13.8" x 11.8" (35cm x 30cm); +/-12 Tilt by hand; Height is adjustable from 37.4"-57" (95cm to 145cm) from the floor via hand adjustable knobs
- **BOTTOM TRAY:** Ventilated tray helps keep media devices cool; Has a surface of 14.3" x 11.8" (36.3cm x 30cm) and it sits at 27" (68.5cm) tall
- **FLEXIBLE SETUP:** Setup a presentation workstation with a projector and laptop to easily transport the trolley between classrooms, boardrooms/conference rooms; Arrange your projector and laptop/notebook computer on either shelf depending on your setup needs
- **SECURE & ORGANIZE DEVICES:** Portable projector stand w/sturdy platforms that have safety ledges to keep devices in place; Thin openings can be used to run straps to secure devices (straps not incl); Incl 2x cable management clips can be attached along pole

Performance

Warranty	5 Years
General Specifications	Top Tray Capacity: 22 lb [10 kg]
	Top Tray Tilt: +/-12 degrees
	Top Tray Height Adjustability: 37.4 in - 57 in [95 cm to 145 cm]
	Bottom Tray Capacity: 22 lb [10 kg]
Height Adjustment	Yes
Minimum Height	37.4 in [950 mm]
Maximum Height	57.1 in [1450 mm]

Physical Characteristics

Color	Black
Material	Steel

Product Length	19.8 in [50.2 cm]
Product Width	17.9 in [45.5 cm]
Product Height	57.1 in [145.0 cm]
Weight of Product	23.3 lb [10.6 kg]

Packaging Information

Package Quantity	1
Package Length	16.5 in [41.8 cm]
Package Width	32.8 in [83.3 cm]
Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	22.7 lb [10.3 kg]

What's in the Box

Included in Package	1 - Projector Platform
	1 - Laptop Platform
	1 - Support Pole
	1 - Base Cross Member
	2 - Base Feet
	2 - Cable Clips
	5 - M6 x 65mm Bolts
	9 - Washer, Type1
	8 - Nuts
	4 - M6 x 12mm Screws
	2 - M6 x 30 Screws
	3 - M6 X 50 Screws, Type1
	1 - Washer, Type2
	1 - M6 X 50 Screws, Type2

1 - Wrench

1 - Hex Key

2 - Casters w/ brakes

2 - Casters w/o brakes

3 - Knobs

2 - Mounting Brackets

**Warranty
Information**

Warranty

5 Years

****Product appearance and specifications are subject to change without notice.***