

1U Adjustable Mounting Depth Vented Rack Mount Shelf - Heavy Duty Fixed Rack Shelf - 250lbs / 113kg

Product ID: ADJSHELFHDV



StarTech.com

The ADJSHELFHDV 1U Adjustable Heavy Duty Vented Rack Mount Shelf lets you add a high-capacity, adjustable 1U shelf to virtually any standard 19-inch server rack or cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This heavy duty rackmount shelf can be adjusted from 19.5in to 38in (mounting depth) to fit your rack, while the vented design improves air flow and help to lower temperatures in the rack. Constructed using 1.2mm SPCC commercial grade cold-rolled steel, providing the ability to hold up to 113kg (250lbs) of equipment - a durable solution for storing large, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

Applications

- For use with all 19" wide Server Racks and Cabinets
- Adding a storage shelf to shallow depth network switches/equipment racks
- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment

Features

- Fits all standard 19" server racks
- SPCC 1.2mm Cold-rolled steel construction

- 1U Heavy Duty Adjustable Vented Rackmount Shelf
- Holds up to 113kg (250lbs)
- Adjustable mounting depth from 19.5in to 38in
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front and Rear)

Performance

Weight Capacity (Stationary)	250.0 lb [113.1 kg]
------------------------------	---------------------

Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.0 in [1.2 mm]
Product Length	27.6 in [70.0 cm]
Product Width	17.7 in [45.0 cm]
Product Height	1.7 in [44.0 mm]
Weight of Product	11.6 lb [5.2 kg]
Maximum Mounting Depth	38.3 in [97.4 cm]
Minimum Mounting Depth	19.5 in [49.5 cm]

Packaging Information



Package Length	30.3 in [77.0 cm]
Package Width	20.8 in [52.8 cm]
Package Height	3.3 in [84.0 mm]
Shipping (Package) Weight	15.5 lb [7.0 kg]

What's in the Box

Included in Package	1U High Cap Adjustable Rack Shelf
	M5 Panel Screws
	Instruction Manual
	Front Mounting Brackets
	Rear Mounting Brackets

****Product appearance and specifications are subject to change without notice.***

