

1-Port 10Gbps PoE++ Injector, 60W, 2.5/5/10G Ethernet/10/100/1000M, PoE++ (802.3af/at/bt), Wall Mountable, Unmanaged Inline Power Over Ethernet, TAA

Produkt-ID: AF31XC-POE-INJECTOR



This 1-Port multi-speed PoE++ Injector serves as a Power Sourcing Equipment (PSE) device and enables Ethernet speeds of 10/100 Mbps/1000Mbps and 1/2.5/5/10Gbps. This TAA-compliant mid-span inline injector can transmit network data and power up to 328ft (100m) for single Powered Devices (PD).

Single port PoE+ injector supports the IEEE 802.3af and 802.3at PSE standards, and delivers up to 60W output (54V, 1.11A). Connect a remote PoE device to a network at a location where there is no power source, but an Ethernet cable already exists. This includes access points, IP cameras, VoIP phone systems, IPTV and access controls. The flexible design of the PoE injector allows for either desktop or surface-mount use.

All Ethernet cables can be routed from one side of the unit for efficient and organized cable management. The compact design (4x2.3x1.3-inch / 100x58.4x33.4mm) ensures straightforward integration into existing network infrastructure, saving space and time during installation.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **10G POE++ INJECTOR:** Single-port TAA-compliant PoE midspan injector supports up to 10Gbps and 60W of power (PoE/PoE+/PoE++); Features OVP, OCP, and SCP protection for enhanced reliability and durability, and a fan-less design to ensure silent operation
- **MULTIGIGABIT 60W DATA & POWER:** Auto-negotiation between 10/100/1000Mbps/2.5G/5G/10G; Delivers 10Gbps data & up to 60W of power to a single powered device up to 262ft (80m) away, up to 5Gbps and 60W of power up to 328ft (100m)
- **HASSLE-FREE INSTALLATION:** Internal power supply and integrated wall-mounting ears with front-facing screw holes offer convenient, versatile installation, especially in hard-to-reach areas; Cables can be routed from one side for better cable management
- **APPLICATIONS:** Provides more power and bandwidth over a single RJ45 connection to demanding PoE devices such as high resolution IP cameras and enterprise grade Wi-Fi 6/6E or 7 access points (APs); Ideal for remote IP devices without available power outlets
- **TECH SPECS:** RJ45 Shielded Socket (data/data+power); 60W max output; 54V 1.7A output; Compliant with IEEE 802.3af/at & IEEE 802.3bt; 10/100/1000 Mbps & 1/2.5/5Gbps; Dimensions 4x2.3x1.3-inch (100x58.4x33.4mm)

Hardware

Garantiebestimmungen	2 Years
Ports	1
Industrienormen	IEEE 802.3af Type 1 / PoE (15.4 W) IEEE 802.3at Type 2 / PoE+ (30 W) IEEE 802.3bt Type 3 / PoE++ (60 W) IEEE 802.3an (10GBASE-T) IEEE 802.3bz (5GBASE-T) IEEE 802.3bz (2.5GBASE-T) IEEE 802.3ab (1000BASE-T) IEEE 802.3u (100BASE-TX) IEEE 802.3i (10BASE-T) IEC 61000-4-2 Level-4 ESD protection (8kV contact/15kV air)

Chipset-ID SkyWorks - Si3471A-A01

Leistung

Wake On Lan	Ja
Max. Datenübertragungsrate	10Gbps
Max. Kabellänge	328.0 ft [100 m]
Kompatible Netzwerke	10G/5G/2.5G/1G/100Mbps/10Mbps
Auto MDIX	Ja
PXE	Ja
Jumbo Frame Support	9K max.
Unterstützte Protokolle	Wake-on-LAN (WoL)

Steckverbinder

Steckverbinder A	1 - RJ-45 (PoE++)
Steckverbinder B	1 - RJ-45

Software

Betriebssystemkompatibilität	Keine Treiber oder Software erforderlich
------------------------------	--

Anzeiger

LED-Anzeiger	1 - LED Indicator
	Solid Green: PoE Injector is receiving power
	1 - PoE Indicator
	Solid Green: Indicates PoE has been negotiated and power is being supplied to the Powered Device

Strom

Eingangsspannung	100 - 240 AC
Eingangsstrom	1.5 A
Ausgangsspannung	54 DC

Ausgangsstrom 1.11 A

Umgebungsbedingungen

Betriebstemperatur 32°F to 104°F (0°C to 40°C)
Lagertemperatur -22°F to 176°F (-30°C to 80°C)
Feuchtigkeit 5~90 % RH (nicht kondensierend)

Physische Eigenschaften

Farbe Schwarz
Gehäusetyp Kunststoff
Produktlänge 4.8 in [12.2 cm]
Produktbreite 2.3 in [5.8 cm]
Produkthöhe 1.3 in [3.4 cm]
Produktgewicht 7.0 oz [198.0 g]

Verpackungsinformationen

Paketmenge 1
Paketlänge 4.9 in [12.4 cm]
Paketbreite 8.3 in [21.0 cm]
Pakethöhe 2.0 in [5.0 cm]
Versandgewicht (Verpackung) 1.1 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten
1 - PoE Injektor
1 - 1,8m NA Stromkabel
1 - Kurzanleitung

Garantieinformatio

nen

Warranty

2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.