

## Desk-Mount Dual Monitor Arm - Full Motion Articulating - Premium

Product ID: ARMDUAL30



Customize your workspace like never before with this premium desk-mount dual monitor arm. It supports two VESA (75x75, 100x100) monitors, side-by-side or stacked. The full-motion articulating arms with spring-assisted height adjustment let you reposition your monitors with ease.

Create a dual-monitor setup to suit your needs, using the interchangeable arms with quick-connect assembly.

In a horizontal setup, the dual-monitor mount supports two monitors from 12" to 30". It's ideal for numerous uses including graphic design, photo editing and many others.

As a vertical monitor stand, the dual-monitor arm supports two monitors from 12" to 24". A stacked setup makes it easy to compare information on two screens without scrolling. Please note: To support two stacked 24" monitors, the height of each monitor (including the bezel around the display) cannot exceed 14" (35 cm).

The adjustable dual monitor arm offers a full range of motion on several axes, letting you tilt, pan and rotate. Switch from landscape to portrait viewing.

Raise or lower your monitors with one smooth motion, using the spring-assisted height adjustment. Adjust the tension to your own preference.

With its steel and aluminum construction, the dual monitor mount supports a weight capacity of 19.8 lb. (9 kg) per arm.

The quick slide-and-click connections make the dual-monitor mount easy to assemble. Clamp the monitor mount to the side of your desk or table (using the pre-installed desk clamp) or attach it through a grommet hole.

The TAA compliant ARMDUAL30 is backed by a 10-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Improve workstation ergonomics in commercial, business and home-office environments
- Use a dual-monitor setup for customer service, web design, financial analysis and other uses
- Mount your displays to your desk or table, using the desk clamp or grommet hole mount

## Features

- Create a dual-monitor setup, side by side (for up to 30" monitors) or stacked (for up to 24" monitors)
- Easy tool-less assembly, and interchangeable arms for flexible setup
- Durable steel and aluminum construction supports a weight capacity of 19.8 lb. (9 kg) per arm
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 50.8"/129 cm)
- Full-motion arms with articulation and spring-assisted height adjustment

---

<b>Hardware</b>	Warranty	2 Years
	Wallmountable	No
	Articulating	Yes
	# of Displays Supported	2
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

---

<b>Performance</b>	Weight Capacity (Per Display)	19.9 lb [9 kg]
	Maximum Display Size	30in
	Height Adjustment	Yes
	Minimum Height	7.9 in [2 cm]
	Maximum Height	28.9 in [7.4 cm]
	Maximum Arm Extension	23.2 in [5.9 cm]
	Swivel / Pivot	360 around the support post
	Display Rotation	180 at the shoulder

360 at the elbow

360

---

<b>Physical Characteristics</b>	Color	Silver & Black
	Material	Steel, Aluminum and Plastic
	Product Length	18.7 in [4.8 cm]
	Product Width	24.3 in [6.2 cm]
	Product Height	17.8 in [4.5 cm]
	Weight of Product	14.0 lb [6.3 kg]

---

<b>Packaging Information</b>	Package Length	20.9 in [5.3 cm]
	Package Width	15.4 in [3.9 cm]
	Package Height	5.5 in [1.4 cm]
	Shipping (Package) Weight	17.4 lb [7.9 kg]

---

<b>What's in the Box</b>	Included in Package	2-in-1 desk or grommet mount
	Included in Package	M6 Allen key
	Included in Package	M3 Allen key
	Included in Package	base cushion
	Included in Package	spring arms
	Included in Package	swivel arms
	Included in Package	VESA monitor mounts
	Included in Package	thumb screws
	Included in Package	quick release cable managers
	Included in Package	dual mount
Included in Package	instruction manual	

---

***\*Product appearance and specifications are subject to change without notice.***

