

## Desk Mount Monitor Arm with 2x USB 3.0 ports - Pole Mount Full Motion Single Arm Monitor Mount for up to 34" VESA Display - Ergonomic Articulating Arm - Desk Clamp/Grommet

**Product ID:** ARMPIVOT2USB3

Save space with this premium desk mount monitor arm, by suspending your screen above your desk.

Use the single arm monitor mount to mount your VESA mount monitor (75x75, 100x100) up to 34".

Made of aluminum, the VESA mount monitor stand provides stable support for your display, with a weight capacity of up to 17.6 lb. (8 kg). Built-in USB 3.0 ports provide convenient connectivity for your computer.

The arm extends 20.2" (514 mm) to allow a wide range of motion. Move the monitor holder arm effortlessly side to side to adjust your screen.

With its articulating arm, the monitor mount makes it easy to find the right viewing angle. Pan +90/-90 degrees left or right and tilt your display +90/-90 degrees up or down. For landscape or portrait viewing, rotate your display +90/-90 degrees.

Work in comfort with this height adjustable monitor stand that lets you raise or lower the monitor arm along the pole, up to 24.4" (620 mm).

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales

The ARMPIVOT2USB3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Mount your VESA mount display to the side of your desk or table in commercial, industrial or office setting
- Use the grommet or c-clamp to mount your display to your desk in a cubicle to save space
- Create a more ergonomic work-space in a business or home office

## Features

- **34 INCH HEAVY DUTY MONITOR MOUNT:** VESA 75x75/100x100mm compatible articulating single monitor mount supports 1 display up to 34" (17.6lb/8kg) w/ full motion articulation & 2 USB 3.0 passthrough ports
- **EASY INSTALLATION:** Tighten c-clamp from top w/ incl. tool or grommet mount to secure to desktop (10mm-50mm); Easily mount display w/ detachable VESA plate; tools incl. to adjust articulation tension
- **WIDE RANGE OF MOTION:** Ergonomic monitor arm increases comfort & productivity w/ +/-90 tilt, +/-90 swivel, 90 rotating screen (landscape/portrait) & toolless adjustable height along 11.8"/300mm pole
- **ONE-TOUCH ADJUSTMENT:** Pole & arm design allows a max height of 24.4" from the desk, with the full motion arm offering toolless 10" height adjustability and outward extension up to 18.4"
- **CONVENIENT CONNECTIVITY:** This desk mount monitor arm includes 2 USB 3.1 Gen 1 5Gbps passthrough ports

that extend your PC/laptop/computer/dock ports for connecting devices & built-in cable management

---

<b>Hardware</b>	Warranty	2 Years
	Wallmountable	No
	Articulating	Yes
	# of Displays Supported	1
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 1.97 in. (10 - 50 mm) Grommet Clamp: Table Thickness 0.39 - 1.97 in. (10 - 50 mm)

---

<b>Performance</b>	Weight Capacity (Per Display)	17.7 lb [8 kg]
	Minimum Display Size	17in
	Maximum Display Size	34"
	Height Adjustment	Yes
	Maximum Height	24.4 in [6.2 cm]
	Maximum Arm Extension	20.2 in [5.1 cm]
	Display Tilt	+90 / - 90
	Display Swivel	+90 / - 90
	Swivel / Pivot	+/- 90 around the support post
	Display Rotation	+/- 180 at the shoulder
		+/- 90 at the elbow
		+90 / - 90

---

<b>Physical Characteristics</b>	Color	Black
	Material	Aluminum
	Product Length	23.4 in [5.9 cm]
	Product Width	1.4 in [35 mm]
	Product Height	24.4 in [6.2 cm]
	Weight of Product	7.2 lb [3.2 kg]

---

<b>Packaging Information</b>	Package Length	9.4 in [2.4 cm]
------------------------------	----------------	-----------------



Package Width	17.1 in [4.4 cm]
Package Height	4.6 in [1.2 cm]
Shipping (Package) Weight	9.2 lb [4.2 kg]

---

<b>What's in the Box</b>	Included in Package	Base Assembly
	Included in Package	Lower Arm
	Included in Package	Upper Arm
	Included in Package	Pole
	Included in Package	VESA Plate
	Included in Package	Arm Shoulder
	Included in Package	Tool Holder
	Included in Package	Cable Management Clip
	Included in Package	Grommet Plate
	Included in Package	Grommet Screw
	Included in Package	3mm Hex Key
	Included in Package	6mm Hex Key
	Included in Package	M4 x 12mm Screws
	Included in Package	M5 x 12mm Screws
	Included in Package	Washers

---

***\*Product appearance and specifications are subject to change without notice.***

