

Desk Mount Dual Monitor Arm - Desk Clamp VESA Compatible Monitor Mount for up to 32 inch Displays - Ergonomic Articulating Monitor Arm - Height Adjustable/Tilt/Swivel/Rotating

Product ID: ARMDUAL3



Create a sleek and elegant two-monitor set-up while saving space. This stylish desk mount dual monitor arm brings you a cost-effective and versatile solution to an ergonomic workspace. Enjoy a wide range of motion with the dual swivel arms plus tilt, pan, rotation and height adjustment.

The multi monitor mount gives you the flexibility to set-up your desktop your way. Each of the articulating arms extends a full 15.2" (38.6 cm) to adjust to your needs.

The flexible dual-swivel arms make it easy to position your monitors. You can place your monitors to face you, or even turn your monitors right around, 180-degrees, to share your screen with others.

The attractive dual monitor mount utilizes a contoured design made of durable aluminum, with an attractive high gloss black finish. The two-monitor arm securely supports two VESA mount (75x75, 100x100) monitors up to 32", with a weight capacity of 17.6 lb. (8 kg) per monitor.

The double monitor arm lets you smoothly and effortlessly adjust the position of your screens for optimum viewing. Tilt your monitors +30/-30 degrees. Swivel +90/-90 degrees to the left or right. Rotate your monitors to portrait or landscape position with the 360-degree rotary VESA plate.

Adjust your monitors to the desired height. The dual screen mount is height adjustable along the 15.7" (39.8 cm) pole.

The multi monitor mount is easy to install, using the C-clamp to attach the mount to the edge of your desk, table, or counter. A keyhole design on the VESA mount makes it easy to slide your monitor onto the mount, then tighten into place. Built-in cable management helps to keep your cables neatly tucked away.

ARMDUAL3 is backed by a StarTech.com 5-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount two displays to your desk, table or counter using the desk clamp
- Create a dual-monitor set-up in commercial offices or customer-facing environments
- Rotate displays to portrait orientation for web design and coding

Features


- **32 INCH LARGE MONITOR SUPPORT:** VESA 75x75mm / 100x100mm compatible multi monitor mount supports 2 large monitors up to 32" (17.6 lb / 8 kg) per arm w/ horizontal articulation & basic height adjustment
- **WIDE RANGE OF MOTION:** Double monitor mount increases ergonomic comfort and productivity with +30/-30 tilt, +90/-90 swivel, 360 rotating display, and height adjustment along the 15.7" (39.8 cm) pole
- **ADJUSTABLE SET UP:** Use the desk-clamp (C-clamp) to easily mount and tighten by hand to a desktop (40-85 mm thickness) & cable management clips to hold incl. tools for quick height & angle adjustment
- **EASY DISPLAY ROTATION:** This desk mount dual monitor arm has articulating arms that support toolless monitor rotation from landscape to portrait positioning for viewing longer pages without scrolling
- **SLEEK DESIGN:** Streamlined look w/ small footprint enhances the work area and built-in adjustable cable management clips along the arms and center pole keep cables organized for a presentable workspace

Hardware

Warranty	5 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm)

Performance

Weight Capacity (Per Display)	17.7 lb [8 kg]
-------------------------------	----------------



Maximum Display Size	32in
Height Adjustment	Yes
Maximum Arm Extension	15.2 in [38.6 cm]
Display Tilt	+ 30 / - 30
Display Swivel	+90 / - 90
Swivel / Pivot	+/- 90 around the support post +/- 180 at the shoulder +/- 90 at the elbow
Display Rotation	360

Physical Characteristics

Color	Black
Construction Material	Aluminum
Product Length	4.1 ft [1.2 m]
Product Width	34.3 in [87.0 cm]
Product Height	20.1 in [51.0 cm]
Weight of Product	7.0 lb [3.2 kg]

Packaging Information

Package Length	8.6 in [21.9 cm]
Package Width	17.3 in [44.0 cm]
Package Height	6.1 in [15.6 cm]
Shipping (Package) Weight	9.6 lb [4.4 kg]

What's in the Box

Included in Package	Desk Clamp Assembly, Lower Desk Clamp Assembly, Upper Swivel Arm Assembly
---------------------	---



Pole

Desk Clamp Screws

Pole Assembly Screws

4mm Hex Key

6mm Hex Key

M4 x 12 mm Screws

M5 x 12 mm Screws

Washers

Cable Management Clip

User Manual

****Product appearance and specifications are subject to change without notice.***

