


Single Desk-Mount Monitor Arm - Full Motion - Articulating - Silver

Product ID: ARMPIVOTHD



Free up space while creating a more comfortable and productive work environment. This desk-mount monitor arm makes it easy to mount your VESA mount (75x75, 100x100) display above your desk or table and adjust the height with one touch for ideal viewing. Its sleek silver finish enhances the aesthetics of your workspace.

This heavy-duty aluminum monitor arm helps you save space, by securely mounting a computer monitor from 13" to 34" in size and up to 19.9 lb. (9 kg) in weight. It's ideal for many different office applications, such as healthcare or financial settings, shared workspaces, or when you wish to show your display to clients or colleagues.

The single monitor arm provides one-touch height adjustment, with a gas-spring cylinder that makes it easy to raise or lower your display. Adjust the tension according to the weight of your monitor, so you can re-position the monitor height effortlessly. The monitor mount provides 13.1" (335 mm) of height adjustment.

The full-motion articulating arm makes it easy to find the right viewing angle. Swivel your monitor 180 degrees to share your display. The articulating arm also supports 180-degree rotation, for landscape or portrait orientation. For comfortable viewing, tilt your screen +90 to -90 degrees.

Made of aluminum, the single monitor mount requires minimal assembly and is easy to install with the desk clamp or grommet mount. A detachable VESA mount panel makes it simple to attach or remove your monitor. Built-in cable management helps keep your cables organized.

The ARMPIVOTHD is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal in office applications including shared workstations with multiple users
- Rotate your display from landscape to portrait position for web design or coding

Features

- Mount a VESA (75x75, 100x100) compatible display 12" to 34", flat screen, curved or ultrawide, with a max weight of 19.9 lb. (9 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 33.8"/85.9 cm)
- Smooth one-touch height adjustment (up to 13.1" / 335 mm), with the gas-spring arm
- Durable heavy-duty aluminum construction with attractive silver finish
- Articulating arm rotates and swivels 180 degrees, and provides +90/ -90 degree tilt

Hardware	Warranty	5 Years
	Wallmountable	No
	Cable Management	Yes
	Articulating	Yes
	# of Displays Supported	1
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.34 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)
	Performance	Weight Capacity (Per Display)
	Minimum Display Size	13"
	Maximum Display Size	34"
	Fits Curved Display	Yes
	Fits UltraWide Displays	Yes
	Minimum Height	6.7 in [1.7 cm]
	Maximum Height	19.9 in [5.0 cm]
	Maximum Arm Extension	23.8 in [6.0 cm]
	Display Tilt	+90 / - 90
	Swivel / Pivot	180
	Display Rotation	180

Special Notes / Requirements Note This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 19.9 lb. (9 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 35" (88.9 cm).

Physical Characteristics	Color	Silver
	Material	Aluminum
	Product Length	3.8 in [96.000 mm]
	Product Width	11.2 in [2.8 cm]
	Product Height	20.8 in [5.3 cm]
	Weight of Product	6.8 lb [3.1 kg]

Packaging Information	Package Length	19.5 in [5.0 cm]
	Package Width	12.6 in [3.2 cm]
	Package Height	4.4 in [1.1 cm]
	Shipping (Package) Weight	9.9 lb [4.5 kg]

What's in the Box	Included in Package	spring arm
	Included in Package	VESA monitor mount
	Included in Package	grommet base plate
	Included in Package	grommet plate
	Included in Package	L bracket
	Included in Package	desk clamp
	Included in Package	clamp screws
	Included in Package	hex key holder
	Included in Package	grommet knob
	Included in Package	rubber pads
	Included in Package	4 mm hex key
	Included in Package	M4x12 mm thumbscrews
	Included in Package	M5x12 mm screws
	Included in Package	washers
	Included in Package	spacers
	Included in Package	instruction manual
	Included in Package	6 mm hex key
	Included in Package	5 mm hex key
Included in Package	grommet screw	



****Product appearance and specifications are subject to change without notice.***

