

Single Monitor Desk Mount - Single Screen Heavy Duty Pole Mount for up to 8kg VESA Compatible Displays - Ergonomic Height Adjustable Monitor Arm Mount - Desk Clamp/Grommet

Product ID: ARMPIVOTV2



Save valuable desk space and position your monitor in a more comfortable viewing position. Constructed of high-grade steel, this monitor desk mount for up to 34" monitors makes it easy to suspend your display above your desk or other work surface.

Clear up your desk surface while creating an ergonomic workspace. This simple yet rugged single monitor mount supports displays 13" to 34" in size and up to 17.6 lb. (8 kg) in weight.

With the height adjustable monitor arm, you can also adjust the height of your monitor along the vertical pole to a maximum height of 17.3" (439 mm) to your desired position, to help reduce neck and eye strain.

Easily rotate, tilt and swivel, to adjust your screen position and find the perfect viewing angle.

The heavy duty monitor arm is made of steel for long-lasting performance. The surface finish features a powder coating to help resist scratches.

The desk clamp monitor mount makes it easy to mount a VESA mount compatible display above your desk, using the included C-clamp or grommet mount. A detachable VESA panel enables simple attachment of your monitor, then you just slide your monitor onto the mount. To help keep your work area free of clutter, the monitor mount also features cable management clips that keep your cables neatly out of sight.

The ARMPIVOTV2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create a more ergonomic workspace in office environments

- Rotate your display from landscape to portrait position for web design or coding
- Mount a display to a desk, table or counter to save space in commercial environments

Features

- **LARGE MONITOR MOUNT:** VESA 75x75mm/100x100mm compatible heavy-duty steel single monitor mount for a large 32" (16:9) or 34" (21:9/ultrawide) up to 17.7lb/8kg w/ height adjustment along the pole
- **WIDE RANGE OF MOTION:** Ergonomic monitor arm increases comfort & productivity w/ +/-45 tilt, +/-90 swivel, 360 rotating screen (landscape/portrait) and adjustable height of 17.3" along the pole
- **EASY INSTALLATION:** Secure monitor mount to desk by hand w/ the c-clamp (10-88mm) or grommet mount (10-75mm); detachable VESA plate w/ quick release clip; tools incl. to adjust articulation tension
- **ORGANIZED WORKSPACE:** Cable Management clips keep computer monitor cables & included articulation tools out of sight & can be mounted anywhere along the pole, keeping your workstation desktop tidy
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This monitor mount is backed for 5-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	100x100 mm 75x75 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

Performance

Weight Capacity (Per Display)	17.7 lb [8 kg]
Minimum Display Size	13"
Maximum Display Size	34"

Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Maximum Height	17.3 in [43.9 cm]
Maximum Arm Extension	3.5 in [88 mm]
Display Tilt	+ 45 / - 45
Swivel / Pivot	+90 / -90
Display Rotation	360

Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 17.7 lb. (8 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 28" (71 cm).
------	--

Physical Characteristics

Color	Black
Material	Steel and Plastic
Product Length	4.5 in [11.4 cm]
Product Width	21.6 in [54.8 cm]
Product Height	5.8 in [14.8 cm]
Weight of Product	5.2 lb [2.4 kg]

Packaging Information

Package Length	5.0 in [12.8 cm]
Package Width	19.4 in [49.3 cm]
Package Height	4.4 in [11.2 cm]
Shipping (Package) Weight	6.8 lb [3.1 kg]

What's in the



Box

Included in Package	VESA monitor mount
	VESA pole clamp
	pole
	pole screws
	desk clamp
	grommet plate
	grommet collar
	cable-management clip
	rubber pads
	thumbscrew
	4 mm hex key
	6 mm hex key
	M4x12 mm screws
	M4x16 mm screws
	M5x12 mm screws
	M5x16 mm screws
	spacers
	washers
	instruction manual

****Product appearance and specifications are subject to change without notice.***

