

Desk Mount Quad Monitor Arm – Premium Articulating VESA 4 Monitor Mount 2x2 up to 30" – Ergonomic Height Adjustable Pole Mount - Tilt/Swivel/Rotate - C-Clamp/Grommet - Silver

**Product ID:** ARMQUADPS



Create a highly productive ergonomic workspace with this premium quad monitor mount, supporting four monitors up to 27" each. Four articulating monitor arms feature dual-swivel action, providing a wide range of motion side to side. The attractive silver finish enhances the aesthetics of your workspace.

The articulating monitor mount lets you maximize your productivity and work in comfort. Each of the four articulating monitor arms extends a full 16.5" (420 mm) and offer a wide range of motion on several axes. Adjust the position of each screen effortlessly as you work.

Made of robust aluminum, the four-monitor setup provides stable support for VESA compatible monitors (75x75, 100x100) with a weight capacity of up to 24.8 lb. (11.25 kg) per display. The cable-management channel helps to keep your workstation neat and tidy.

Share your screen with ease. The four arm monitor mount offers a full +180-degree / -180-degree pan, to move your screen left or right. It tilts freely +90 / -15 degrees to adjust the angle up or down. Rotate your screens for landscape or portrait viewing.

Work in comfort. This height adjustable monitor mount lets you raise or lower the monitor arms along the 708 mm (27.9") pole.

The fully assembled desk clamp and pole, plus quick slide-and-click connections, ensure easy assembly. It also saves time when setting up multiple units. The four screen mount gives you the option of desk clamp or grommet hole mounting (hardware included).

The TAA compliant ARMQUADPS is backed by a StarTech.com 10-year warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**

## Applications

- Mount four displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your displays for four-screen access in a media room
- Rotate displays to portrait orientation for web design and coding

## Features

- **HEAVY DUTY MULTI-MONITOR MOUNT:** VESA 75x75/100x100mm compatible desk mount quad monitor arm (2x2) supports 4 large displays up to 30" (24.8lb) per screen; Articulating & height adjustable
- **EASY INSTALLATION:** Premium desktop quad monitor mount w/ convenient toolless slide & click design makes assembling the monitor arms & VESA adapters easy; Desk & grommet clamps can be tightened by hand
- **WIDE RANGE OF MOTION:** Ergonomic monitor mount w/ +90/-15 tilt, +/-180 swivel, 360 rotation, adjustable height along 27.9" pole; Swiveling arms for flexible LCD/LED monitor setup ie. back to back
- **ADJUSTABLE SET UP:** Silver four monitor mount w/ cable management clips along arms & center pole to organize cables for a tidy computer workspace & holds incl. adjustment tools for articulation tension
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This quad monitor arm is backed for 10-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

---


### Hardware

Warranty	10 Years
Cable Management	Yes
Articulating	Yes
# of Displays Supported	4
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)

---

### Performance

Weight Capacity (Per Display)	24.9 lb [11.2 kg]
-------------------------------	-------------------



Minimum Display Size	13"
Maximum Display Size	27in
Height Adjustment	Yes
Maximum Arm Extension	16.5 in [42 cm]
Maximum Arm Span	37.0 in [94 cm]
Display Tilt	+90 / -15
Display Swivel	+180 / -180
Display Rotation	360

---

**Physical Characteristics**

Color	Silver
Material	Aluminum
Product Length	16.5 in [42.0 cm]
Product Width	37.0 in [94.0 cm]
Product Height	35.8 in [91.0 cm]
Weight of Product	21.0 lb [9.5 kg]

---

**Packaging Information**

Package Length	34.8 in [88.5 cm]
Package Width	10.6 in [27.0 cm]
Package Height	13.6 in [34.5 cm]
Shipping (Package) Weight	28.1 lb [12.7 kg]

---

**What's in the Box**

Included in Package	Pole Assembly
	Shoulders
	Swivel Arms
	VESA Mounts



Upper Desk Clamp

Lower Desk Clamp

Grommet Adapter Plate

EVA Foam Pad

Grommet Clamping Plate

Cable Management Clips

VESA Screws

M3 Hex Keys

M5 x 14 mm Hex Screws

User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

