

Desk Mount Monitor Arm with 2x USB 3.0 ports - Slim Full Motion Adjustable Single Monitor VESA Mount up to 8kg Display - Ergonomic Articulating Arm - Desk Clamp/Grommet

**Product ID:** ARMSLIM2USB3



Free up space while creating an ergonomic work environment. This desk-mount monitor arm makes it easy to securely mount and adjust a 17" to 34" display above your desk.

The single arm monitor mount extends up to 18.4" (467 mm) so it's easy to find the right viewing angle. Swivel your monitor +90/-90 degrees or tilt your screen +90/-90 degrees for comfortable viewing. You can even rotate it 90 degrees for landscape or portrait viewing.

With up to 17.5" (445 mm) of height adjustment, the slim monitor-mount arm features a mechanical spring that makes it easy to raise or lower your display offering a toolless adjustable height range of 10.1". Adjust the tension according to the weight of your monitor for effortless movement.

The VESA mount monitor stand is easy to install (desk C-clamp or grommet mount) and offers built-in cable management and dual USB 3.0 port passthrough for connecting your computer. The detachable VESA mount makes it simple to attach your monitor.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ARMSLIM2USB3 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Rotate your display from landscape to portrait position for web design or coding

- Ideal in office applications including shared workstations with multiple users
- USB pass-through ports simplify cable management for your peripherals
- .

## Features

- **HEAVY DUTY MONITOR MOUNT:** VESA 75x75/100x100mm compatible slim single monitor mount for a large 32" (16:9) or 34" (21:9/ultrawide) display up to 17.6lb/8kg; Full motion articulation; 2 USB 3.0 passthrough ports
- **EASY INSTALLATION:** Tighten c-clamp from top w/ incl. tool or grommet mount to secure to desktop (10 mm-50 mm); Easily mount display w/ detachable VESA plate; tools incl. to adjust articulation tension
- **WIDE RANGE OF MOTION:** Articulating ergonomic monitor arm increases comfort & productivity w/ +/-90 tilt, +/-90 swivel, 90 rotating screen (landscape/portrait), & 360 rotating monitor arm
- **ONE-TOUCH ADJUSTMENT:** Max height of 17.5" from the desk, the spring-assisted monitor arm offers toolless adjustable height range of 10.1" and can extend outwards up to 18.4" away from base
- **CONVENIENT CONNECTIVITY:** Desk mount monitor arm includes 2 USB-A 3.1 Gen 1 5Gbps passthrough ports that extend your PC/laptop/computer/dock ports for connecting devices & built-in cable management

---

### Hardware

Warranty	2 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 1.97 in. (10 - 50 mm) Grommet Mount Hole Size: 0.39 - 1.97 in. (10 - 50 mm)

---

### Performance

Weight Capacity (Per Display)	17.7 lb [8 kg]
Minimum Display Size	17in



Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Height Adjustment	Yes
Maximum Height	17.5 in [44.5 cm]
Display Tilt	+90 / - 90
Display Swivel	+90 / - 90
Swivel / Pivot	+/- 180 at the base +/- 180 at the shoulder +/- 90 at the elbow
Display Rotation	90

---

**Physical Characteristics**

Color	Black
Construction Material	Aluminum
Product Length	21.5 in [54.7 cm]
Product Width	4.5 in [11.5 cm]
Product Height	17.5 in [44.5 cm]
Weight of Product	6.3 lb [2.8 kg]

---

**Packaging Information**

Package Length	17.1 in [43.5 cm]
Package Width	9.4 in [24 cm]
Package Height	4.6 in [11.7 cm]
Shipping (Package) Weight	7.7 lb [3.5 kg]

---

**What's in the Box**

Included in Package	Base Clamp Assembly
---------------------	---------------------



Lower Arm

Upper Arm

VESA Mount

Tool Clip

Grommet Plate

Grommet Screw

3mm Hex Key

6mm Hex Key

M4 x 12mm Screws

M5 x 12mm Screws

Washers

---

***\*Product appearance and specifications are subject to change without notice.***

