

## Single Desk-Mount Monitor Arm - Full Motion Articulating - Steel

Product ID: ARMSLIM



This slim, articulating desk-mount monitor arm lets you mount a flat-panel display to free up space on your desk or table. The full motion articulating arm makes it easy to position your monitor for the perfect viewing angle and optimal comfort.

With a stylish, slim design that looks great and takes up only a small amount of desk space, the single monitor arm lets you locate your display as needed while reclaiming valuable workspace. The monitor mount supports 12" to 34" displays with a maximum weight capacity of 15 lb. (7 kg). Mounting your display above the desk surface enables you to adjust your display height, position and viewing angles easily, for an ergonomic work environment.

The full motion mount lets you extend the arm a full 23.46" (596 mm). Position your monitor for ideal viewing with the articulating monitor arm. You can tilt and swivel your display with a full range of motion across multiple axes. The spring-assisted height adjustment lets you raise or lower your monitor with smooth and effortless positioning. For viewing longer pages or blocks of code without having to scroll down your screen, the adjustable monitor arm also supports landscape-to-portrait display rotation.

With its durable steel construction, the display mount securely holds your computer monitor. Setting up is easy. You can either clamp the mount to the side of your desk or table, or mount it through a grommet hole (hardware included). The adjustable arm features a helpful indicator area to help configure the desired level of resistance for moving the display. The integrated cable management channel keeps things neat and organized.

The TAA compliant ARMSLIM monitor arm is backed by a StarTech.com 10-year warranty and free, lifetime technical support.

### Certifications, Reports and Compatibility



## Applications

- Mount a display to the side of your desk, table or counter with a wide range of adjustment capability
- Grommet mount your display through a desk and position as needed
- Rotate displays to portrait orientation for web design and coding

## Features

- Mount a VESA (75x75, 100x100) compatible display 12" to 34", flat screen, curved or ultrawide, with a max weight of 15.5 lb. (7 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 33.9"/86.1 cm)
- Full range of motion with articulating arm: +90/-65 degree tilt, 360 degree swivel and 360 degree rotation around the support pole and the elbow
- Maximum arm extension of 23.46" (596 mm)
- Easy to re-position with spring-assisted height adjustment and a gauge to indicate the level of resistance

<b>Hardware</b>	Warranty	10 Years
	Articulating	Yes
	# of Displays Supported	1
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)
<b>Performance</b>	Weight Capacity (Per Display)	15.5 lb [7 kg]
	Maximum Display Size	34"
	Fits Curved Display	Yes
	Fits UltraWide Displays	Yes
	Height Adjustment	Yes
	Maximum Arm Extension	23.5 in [6.0 cm]
	Display Tilt	+90 / -65
	Display Swivel	360
	Swivel / Pivot	180 around the support post
	Display Rotation	360 at the elbow +90 / - 90

<b>Special Notes / Requirements</b>	Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 15.5 lb. (7 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 36" (91.4 cm).
-------------------------------------	------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

<b>Physical Characteristics</b>	Color	Black
	Material	Steel and Plastic
	Product Length	0.0 in [0.000 mm]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	7.0 lb [3.2 kg]

---

<b>Packaging Information</b>	Package Length	18.1 in [4.6 cm]
	Package Width	13.7 in [3.5 cm]
	Package Height	5.1 in [1.3 cm]
	Shipping (Package) Weight	9.3 lb [4.2 kg]

---

<b>What's in the Box</b>	Included in Package	Articulating Monitor Arm
	Included in Package	2-in-1 Desk / Grommet Clamp
	Included in Package	Thumb Screws
	Included in Package	6mm Allen Wrench
	Included in Package	3mm Allen Wrench
	Included in Package	Instruction Manual

---

**\*Product appearance and specifications are subject to change without notice.**

