

Desk Mount Dual Monitor Arm - Ergonomic Dual Monitor VESA Mount 32" (17.6lb) Displays - Crossbar Handle for Synchronized Full Motion - Height Adjustable - C-Clamp/Grommet

Product ID: ARMSLMBARDUO



This Dual Monitor Arm lets you mount two 17" to 32" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable crossbar design, the adjustable height dual monitor stand lets you create more usable work space by mounting your monitors side by side on a single base.

The computer screen stand features one-touch height adjustment. The smooth +/- 10 tilt motion and +/- 90 swivel make it easy to find the optimal viewing angle. You can also rotate each display 180° for portrait or landscape viewing and laterally adjusted along the crossbar length.

The adjustable dual monitor mount is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ARMSLMBARDUO is backed by a 5-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Ideal in office applications including shared workstations with multiple users
- Rotate your display from landscape to portrait position for web design or coding

## Features

- **DUAL 32 INCH MONITOR ARM:** VESA 75x75/100x100mm compatible heavy-duty desk mount dual monitor arm supports large monitors up to 32" (17.6lb/8kg) per display w/ synchronized full motion articulation
- **ONE-TOUCH ADJUSTMENT:** Max height of 23.4" from desk, the spring-assisted computer monitor arm w/sturdy handle offers synchronized toolless adjustable height range of 13" & can extend outward up to 23"
- **WIDE RANGE OF MOTION:** Ergonomic monitor arm increases comfort w/ individual monitor +/-10 tilt, +/-10 swivel, 360 rotating; sliding horizontal crossbar for screen alignment can also swivel 180
- **EASY INSTALLATION:** C-clamp or grommet mount secures to desk (10mm to 48mm); detachable VESA plate w/ quick release clip makes mounting displays easy; tools incl. to adjust articulating tension
- **SMALL FOOTPRINT:** Universal desktop multi-monitor mount w/space-saving design enhances the work area & built-in adjustable cable management channels along the arms w/ covers keep cables organized

<b>Hardware</b>	Warranty	2 Years
	Wallmountable	No
	Articulating	No
	# of Displays Supported	2
	Mounting Options	Desk & Grommet Clamp
	VESA Hole Pattern(s)	75x75 mm
	VESA Hole Pattern(s)	100x100 mm
	Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.35 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 1.89 in. (10 - 48 mm)
<b>Performance</b>	Weight Capacity (Per Display)	17.7 lb [8 kg]
	Minimum Display Size	17in
	Maximum Display Size	32in
	Height Adjustment	Yes
	Display Tilt	+10 / -10
	Display Swivel	+90 / - 90
	Swivel / Pivot	+/- 90 at the crossbar
	Display Rotation	+/- 180 at the shoulder
		+/- 180 at the elbow
		+180 / -180

<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
	Product Length	32.8 in [8.3 cm]
	Product Width	22.4 in [5.7 cm]
	Product Height	23.4 in [6.0 cm]
	Weight of Product	16.1 lb [7.3 kg]
<hr/>		
<b>Packaging Information</b>	Package Length	35.2 in [9.0 cm]
	Package Width	8.9 in [2.2 cm]
	Package Height	5.9 in [1.5 cm]
	Shipping (Package) Weight	19.3 lb [8.8 kg]
<hr/>		
<b>What's in the Box</b>	Included in Package	Base Clamp Assembly
	Included in Package	Lower Arm
	Included in Package	Upper Arm
	Included in Package	Cross Bar
	Included in Package	VESA Mount
	Included in Package	Grab Handle
	Included in Package	Grommet Plate
	Included in Package	Base Plate
	Included in Package	Adhesive Foam Pad
	Included in Package	Cable Management Clip, Base
	Included in Package	Button Head Hex Screws
	Included in Package	Flat Head Hex Screws
	Included in Package	3mm Hex Key
	Included in Package	4mm Hex Key
	Included in Package	6mm Hex Key
	Included in Package	M4 x 12 Screws
	Included in Package	M5 x 12 Screws
	Included in Package	Washers
	Included in Package	Countersunk Screws
	Included in Package	Grommet Screw



Included in Package	Upper C Clamp Bracket
Included in Package	Lower C Clamp Assembly

---

***\*Product appearance and specifications are subject to change without notice.***

