

Sit Stand Monitor Arm - Desk Mount Adjustable Sit-Stand Workstation Arm for Single 34" VESA Mount Display - Ergonomic Articulating Standing Desk Converter with Keyboard Tray

Product ID: ARMSTSCP1



This sit-stand monitor arm transforms your desk or tabletop into an ergonomic workstation. The monitor arm features a keyboard tray and easy height adjustment that lets you alternate between sitting and standing, without interrupting your workflow. Move your workstation up or down, left or right, to meet your needs.

Adjust your position, with one smooth motion. Simply lift the work surface up to 17.7" (450 mm), to elevate both your monitor and keyboard. You can adjust the tension to your own preference. The monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column.

This sit-stand monitor arm supports one monitor up to 34". The swing arm swivels +/-90 and tilts +35/ -5for ideal viewing. The VESA mount also rotates up to 360 for portrait or landscape orientation.

The monitor arm features a large keyboard tray (17.68 x 8.15"/ 449 x 207 mm) with ample working space. A slide-out tray (8.5 x 8.4" / 217 x 213 mm) holds your mouse, on the left or right.

To make the most of your workspace, you can tuck the monitor arm away when it's not in use, to free up space. The keyboard tray also folds up to 90.

The compact sit-stand monitor arm features a grommet assembly and desk-clamp option, to fit easily into your workspace, including space-limited corners.

The ARMSTSCP1 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create a sit-stand workstation in healthcare environments, cubicles, or offices with limited space

- Provides a cost-effective solution, with clamp or grommet mounting options for existing desks
- Works well with space-limited corner desks

Features

- **ERGONOMIC SIT-STAND WORKSTATION:** This VESA 75x75mm/100x100mm compatible sit stand monitor arm supports a single display (incl. widescreen) up to 34-inch (17.6lb/8kg) & features horizontal articulation
- **WIDE RANGE OF MOTION:** The articulating ergonomic single monitor arm supports +35/-5 tilt, 360 rotating computer screens (landscape/portrait) & adjustable height along the 4.9" (124mm) track
- **MAXIMIZE DESK SPACE:** This desk mount stand-up workstation has a padded keyboard tray with slide-out right/left mouse tray that folds up 90 when not in use & cable management for a minimal footprint
- **FULLY ADJUSTABLE:** Standing desk converter w/ spring-assisted height adjustment & 360 swivel base is designed for max stability & flexible installation (desk-clamp or grommet) for space-limited areas
- **EASY TO CLEAN:** The removable mouse tray & plastic ergonomic wrist rest cover allow for frequent cleaning of all high-touch surfaces for a sanitary shared office desktop monitor sit stand workstation

Hardware

| | |
|----------------------------|--|
| Warranty | 2 Years |
| Cable Management | Yes |
| # of Displays Supported | 1 |
| Mounting Options | Desk & Grommet Clamp |
| VESA Hole Pattern(s) | 100x100 mm 75x75 mm |
| Mounting Surface Thickness | Desk Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Grommet Clamp: Table Thickness 0.31 - 1.96 in. (8 - 50 mm) Table Hole for Grommet Mount: 0.33 - 2.55 in. (8.5 - 65 mm) |

Performance

| | |
|------------------------|--|
| General Specifications | Weight capacity of monitor arm: 17.6 lb. (8 kg) Weight capacity of keyboard tray with grommet mount: 5.6 lb. (2.5 kg) Weight capacity of keyboard tray with desk clamp: 3.3 lb. (1.5 kg) |
| Maximum Display Size | 34" |



| | |
|-------------------|-----------|
| Height Adjustment | Yes |
| Display Tilt | +35 / -5 |
| Swivel / Pivot | +90 / -90 |
| Display Rotation | 360 |

Physical Characteristics

| | |
|-------------------|-----------------------------|
| Color | Black |
| Material | Steel, Aluminum and Plastic |
| Product Length | 26.2 in [66.6 cm] |
| Product Width | 3.8 ft [1.2 m] |
| Product Height | 3.3 ft [1.0 m] |
| Weight of Product | 25.2 lb [11.4 kg] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Length | 34.9 in [88.7 cm] |
| Package Width | 15.8 in [40.2 cm] |
| Package Height | 8.4 in [21.4 cm] |
| Shipping (Package) Weight | 27.4 lb [12.4 kg] |

What's in the Box

| | |
|---------------------|--------------------|
| Included in Package | monitor arm |
| | column |
| | keyboard tray |
| | keyboard tray cap |
| | base |
| | VESA monitor mount |
| | plastic washer |
| | metal washer |



M8x20 mm screw

M6x25 mm screws

M6x12 mm screws

M6x10 mm screws

M6x8 mm screw

M4x10 mm screws

base screws

2.5 mm hex key

5 mm hex key

6 mm hex key

adhesive strip

socket driver

base pad

base plate

M8x65 mm screw

grommet plate

clamp screws

clamp L bracket

clamp screw assembly

instruction manual

****Product appearance and specifications are subject to change without notice.***

