

## 400 Watt ATX12V 2.01 Computer PC Power Supply w/ 20 & 24 Pin Connector

**Product ID:** ATX2POWER400



This high quality 400 Watt ATX12V 2.01 power supply offers a reliable PC power solution, with support for modern dual-core CPU designs as well as PCI Express and SATA device connections.

Compliant with ATX12V 2.01 revision standards, the power supply offers dual 12V power rails, and ensures broad compatibility with a 20/24 pin motherboard connection.

Designed to provide dependable, long-lasting power to your hard working AMD or Intel CPU based system, the 400 Watt PSU is backed by StarTech.com's 2 year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Offers extra current required by cutting-edge CPUs and peripherals
- Dual 12V rails are designed for demanding components.

### Features

- Rear power cut off switch
- Sleeve Bearing provides increased reliability, air flow and longer life

- High flow fan provides efficient cooling for the system and the power supply
- ATX12V version 2.01 compliant
- EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- PCI Express Connector for next generation video cards
- High quality connectors provide minimal resistance and enhanced electric conductivity
- Quad Protection: Short Circuit Protection, Over Power Protection, Over Voltage Protection and No Load Protection
- Industry's leading safety approval ratings
- Our power supplies are compatible with all leading processors including Pentium 4

---

#### Hardware

Warranty	2 Years
Fans	1 - 80 mm
Fan Bearing Type	Sleeve Bearing

---

#### Performance

Air Flow Rate	32.3 CFM
Noise Level	27.4 dBa
MTBF	100,000 Hrs
Output Power	400W
Power Factor Correction	No
Efficiency Rating	68% (Typical Load)

---

#### Connector(s)

Output Connectors	1 - ATX 12V P4 Power (4 pin, v 2.x)
	1 - ATX Split Power (20+4 pin, v 2.x)
	6 - LP4 (4 pin; Large Drive Power)
	1 - PCI Express Power (6 pin, v 1.x)
	2 - SATA Power (15 pin)
	2 - SP4 (4 pin, Small Drive Power)

---

**Power**

Input Voltage Frequency	50~60 Hz
Current -12.0V (A)	1A
Current +12.0V1 (A)	14A
Current +12.0V2 (A)	15A
Current +3.3V (A)	30A
Current +5.0V (A)	28A
Current +5.0Vsb (A)	2.5A
Input Voltage	115 ~ 230
Input Current	8 ~ 4

---

**Environmental**

Operating Temperature	0 ~ 50
Storage Temperature	-20 ~ 80

---

**Physical Characteristics**

Product Length	5.5 in [14 cm]
Product Width	5.9 in [15 cm]
Product Height	3.3 in [8.5 cm]

---

**Packaging Information**

Package Quantity	1
Package Length	9.1 in [23.1 cm]
Package Width	3.8 in [97 mm]
Package Height	8.5 in [21.6 cm]
Shipping (Package) Weight	5.2 lb [2.3 kg]

---

**What's in the Box**

Included in Package	1 - 400W ATX Power Supply
---------------------	---------------------------

1 - Power Cord (NA)

1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***