

## Conference Table Connectivity Box for A/V - 4K

Product ID: BOX4HDECP2



This conference table connectivity box for A/V installs in your table or lectern to provide A/V, networking, and USB charging connectivity in your boardroom, auditorium, or classroom. The box makes it easy to connect HDMI, DisplayPort and VGA laptops to your room's large HDMI display, and provides LAN and USB power connectivity for charging USB devices. The box also provides some boardroom cable management by hiding connectivity cables in your table.

The table box enables presenters in your conference room to easily share their laptop screen on the room's large display or projector, with supported resolutions up to 4K 30Hz.

To share video from virtually any laptop, the table box supports HDMI, VGA and DisplayPort inputs and automatically outputs the most recently connected input to the HDMI display.

Enabling visitors in your conference room to charge their iPhone, iPad, smartphone, or tablet, the table box features three USB charge ports. Plus, the box features an Ethernet pass-through port to provide secure wired network connectivity in rooms where Wi-Fi isn't available.

The boardroom interconnect box has an aluminum finish that complements your space. The hideaway panel eliminates clutter by discreetly covering the connection ports when they're not in use.

TAA compliant BOX4HDECP2 is backed by a 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Install in tables or podiums

- Use for presenting and video conferencing
- Share video to collaborate in office environments
- Share video conference software to your entire room

## Features

- Easily collaborate by connecting your HDMI, VGA or DisplayPort laptop to your conference room's HDMI display, from a single access point
- Charge your phone or tablet, with three accessible USB charge ports
- Add style and technological sophistication to your conference room or auditorium by building an A/V connectivity box into your table with a pop-up panel that hides ports when they're not in use
- Provide secure, wired network connectivity in your boardroom table with Ethernet pass-through
- Quickly switch between which laptop screen is shared with automatic A/V switching
- TAA compliant

---

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	Active or Passive Adapter	Passive
	AV Input	VGA
	AV Input	3.5 mm Audio
	AV Input	HDMI
	AV Input	DisplayPort
	AV Output	HDMI
	Audio	Yes
	USB Pass-Through	No

---

<b>Performance</b>	Video Revision	HDMI 1.4
	Video Revision	DisplayPort 1.2
	Maximum Cable Length	50.0 ft [15.2 m]
	Maximum Analog Resolutions	1920 x 1200 60Hz
		3840x2160 (4K) 30Hz
	Maximum Digital Resolutions	3840x2160 (4K) 30Hz (HDMI and DP Inputs Only)
		2560x1600 60Hz (HDMI and DP Inputs Only)
	Supported Resolutions	2560x1600 60Hz (HDMI and DP Inputs Only)
	Aspect Ratio	1920x1200 60Hz (Maximum VGA Input)
	Wide Screen Supported	1920x1080 (1080p) 60Hz
1280x720 (720p) 60Hz		

\*\*Lower resolutions and refresh rates, not stated but below the

maximum, may also be supported

16:9

Yes

<b>Connector(s)</b>	Connector A	HDMI (19 pin)
	Connector A	VGA (15 pin, High Density D-Sub)
	Connector A	3.5 mm Mini-Jack (3 Position)
	Connector A	RJ-45
	Connector A	USB Type-A (4 pin) USB 2.0
	Connector A	DisplayPort (20 pin)
	Connector B	HDMI (19 pin)
	Connector B	RJ-45

<b>Special Notes / Requirements</b>	Note	VGA (Input) to HDMI (Output) - HDMI Output Port is Active
		DisplayPort (Input) to HDMI (Output) - HDMI Output Port is Active
		HDMI (Input) to HDMI (Output) - HDMI Output Port is Passive

<b>Power</b>	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Output Voltage	12V DC
	Output Current	2A
	Plug Type	N
	Power Consumption (In Watts)	24

<b>Environmental</b>	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	10% to 85% (non-condensing)

<b>Physical Characteristics</b>	Color	Silver
	Product Length	6.7 in [1.7 cm]
	Product Width	3.9 in [100.000 mm]
	Product Height	3.9 in [98.000 mm]
	Weight of Product	3.8 lb [1.7 kg]



<b>Packaging Information</b>	Package Length	6.7 in [1.7 cm]
	Package Width	3.9 in [100.000 mm]
	Package Height	3.9 in [98.000 mm]
	Shipping (Package) Weight	4.0 lb [1.8 kg]

---

<b>What's in the Box</b>	Included in Package	conference table box
	Included in Package	universal power adapter (NA/JP, EU, UK, ANZ)
	Included in Package	die cut outline
	Included in Package	quick-start guide
	Included in Package	mounting brackets
	Included in Package	cable tie bracket
	Included in Package	cable tie bracket screws

---

***\*Product appearance and specifications are subject to change without notice.***

