

Conference Table Box for AV Connectivity

Product ID: BOX4HDECP



This connectivity box for conference tables features a concealed, in-table design that lets you connect a VGA, Mini DisplayPort, HDMI or composite video source device to an HDMI display or projector. When the video switch isn't in use, you can simply slide the stylish cover panel over the connectors, hiding them inside the table or podium surface.

Presenters can conveniently share content from their own device with the table top switch automatically converting any attached audio/video source device into a single HDMI output. The switch box also offers stylish integration into your modern boardroom or classroom with a discreet hideaway panel. For added convenience the BOX4HDECP features a USB charging port to charge your mobile device and an Ethernet pass-through port for Internet connectivity in boardrooms where Wi-Fi is not available.

The A/V switch makes your large display accessible to any presenter's video source device, by installing directly into the surface of your table or podium, and automatically outputs the most recently connected video source. Plus, support for high-definition video resolutions up to 1920x1080 (1080p) ensures that the quality of your presentation is maintained.

With support for different video inputs, including HDMI, VGA, Mini DisplayPort, and composite, the video switch ensures support for almost any laptop, Ultrabook or mobile device such as MacBook, Microsoft Surface Pro 2 & 3, and Lenovo X1. The switch panel even works with legacy audio/video devices such as DVD players, and supports the use of video adapters for your iPhone or iPad.

The BOX4HDECP is backed by a StarTech.com 2-year warranty, and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Build directly into a boardroom table for video presentations and video conferencing

- Build into a podium, for live presentation control
- Connect your device to a projector or large display and switch from one computer to another, or to a mobile device automatically, to collaborate during a boardroom meeting
- Use in a boardroom or classroom where a projector or display may not have the required connectivity ports
- Hide your unsightly cables and switch box by building directly into your table or podium

Features

- In-table installation
- Automatic audio / video switching
- Hideaway panel
- Supports VGA, HDMI, mDP and composite audio / video sources
- Built-in USB charging port
- Ethernet pass through port for network connectivity
- Supports video resolutions up to 1080p
- Concealed table installation clears boardroom cable clutter
- Enable boardroom connection compatibility with laptops and Ultrabooks
- Single cable connection to your HDMI Display

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
	Passive
AV Input	VGA
	HDMI
	Mini-DisplayPort
	Composite
	3.5 mm Audio
Ports	4



AV Output	HDMI
Audio	Yes
USB Pass-Through	No

Performance

Maximum Cable Length	50.0 ft [15.2 m]
Maximum Analog Resolutions	1920x1080
Maximum Digital Resolutions	1920x1080
Supported Resolutions	1920x1080 (1080p)
Wide Screen Supported	Yes
Audio Specifications	7.1 Surround sound (HDMI, Mini DisplayPort) 2-Channel Stereo (3.5mm, RCA)

Connector(s)

Connector A	HDMI (19 pin)
	VGA (15 pin, High Density D-Sub)
	Composite Video (1 x RCA)
	3.5 mm Mini-Jack (3 Position)
	RJ-45
	USB Type-A (4 pin) USB 2.0
	Mini-DisplayPort (20 pin)
	Stereo Audio (2 x RCA)
Connector B	HDMI (19 pin)
	RJ-45

Special Notes / Requirements

Note	VGA (input) to HDMI (output) - HDMI port is active Composite (input) to HDMI (output) - HDMI port is active DisplayPort (input) to HDMI (output) - HDMI port is active HDMI (input) to HDMI (output) - HDMI port is passive
------	--



Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	12V DC
Output Current	2A
Plug Type	N
Power Consumption (In Watts)	24

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10% to 85% (Non-condensing)

Physical Characteristics

Product Length	6.7 in [17.0 cm]
Product Width	3.9 in [100.0 mm]
Product Height	3.9 in [100.0 mm]
Weight of Product	2.5 lb [1.1 kg]

Packaging Information

Package Length	9.3 in [23.5 cm]
Package Width	6.3 in [16.0 cm]
Package Height	7.5 in [19.0 cm]
Shipping (Package) Weight	3.9 lb [1.8 kg]

What's in the Box

Included in Package	HDMI/VGA/mDP/Composite Table Surface Access Switch
	Universal Power Adapter (NA/EU/UK/AU)
	DieCut Outline



Instruction Manual

****Product appearance and specifications are subject to change without notice.***

