

## 4x 2.5" SSD/HDD Mounting Bracket with Cooling Fan

**Product ID:** BRACKET425F



Increase the performance and data storage capacity of your desktop computer or enhance your server room storage, with this 4-drive mounting bracket kit for 2.5" solid-state drives or hard drives.

This drive-mounting bracket lets you add four 2.5" SSDs or HDDs into two 5.25" front bays of your computer or server, allowing you to enhance your data storage capacity. The mounting brackets supports a wide range of 2.5" SSDs/HDDs from 5 to 15 mm in height.

A large built-in fan keeps air moving to dissipate heat build-up, and ensure optimum operating temperatures. Protecting against excessive heat build-up maximizes the life of your drives. The fan also features a dust filter making the mounting bracket ideal for industrial or corporate environments.

Engineered with steel framing, the mounting bracket is designed for dependable performance and durability. BRACKET425F is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Add the performance and storage capacity of four 2.5" SSD/HDDs, installed into two unused 5.25" bays in your desktop computer or server
- Cooling fan with dust filter makes the mounting bracket ideal for industrial and corporate environments
- Repurpose unused laptop hard drives to work with your desktop computer

### Features

- Mount four SSDs/HDDs into two front bays (5.25") of your desktop computer or server
- Supports 2.5" SSD/HDDs from 5 - 15 mm
- Durable mounting bracket with steel framing
- Cooling fan with filter helps to ensure optimum operating temperature

---

**Hardware**

Warranty	2 Years
Fan(s)	Yes
Fans	80 mm
Number of Drives	4
Drive Size	2.5in
Compatible Drive Types	SATA & IDE
Drive Installation	Fixed
Number of 2.5 inch bays	4
Supported Drive Height(s)	5mm
	7mm
	9.5mm
	12.5mm
	15mm
Fan Bearing Type	Dual Ball Bearing

---

**Performance**

MTBF	50000 hours
------	-------------

---

**Connector(s)**

Host Connectors	LP4 (4 pin, PWM)
-----------------	------------------

---

**Physical Characteristics**

Color	Black
Material	Steel and Plastic



Max Drive Height	0.6 in [15 mm]
Product Length	6.4 in [16.2 cm]
Product Width	5.9 in [15.0 cm]
Product Height	3.3 in [85.0 mm]
Weight of Product	18.4 oz [520.0 g]

---

**Packaging Information**

Package Length	7.0 in [17.9 cm]
Package Width	6.3 in [16.1 cm]
Package Height	3.4 in [87.0 mm]
Shipping (Package) Weight	22.2 oz [628.0 g]

---

**What's in the Box**

Included in Package	SSD/HDD mounting bracket with fan mounting screws pack quick start guide
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***

