


2ft CAT6 Ethernet Cable - Green CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Molded Network/Patch Cord w/Strain Relief/ Individually Tested

ID prodotto: C6PATCH2GN



The C6PATCH2GN Cat 6 Patch Cable (2 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable green PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Gigabit Patch Cable delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Our Cat6 Ethernet Cables are ETL Verified to meet ANSI/TIA-568.2-D standards, ensuring peak performance for high-speed 10G applications. Independent testing confirms compliance with strict insertion loss, return loss, and crosstalk limits, maintaining stable signal transmission over longer

runs. The STP shielding is verified for EMI resistance, for guaranteed reliability in demanding environments.

## Certificazioni, report e compatibilità



## Applicazioni

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

## Caratteristiche

- Constructed with top quality components
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Individually Tested to comply w/ANSI/TIA-568-2.D Category 6; ETL Verified to meet ANSI/TIA-568.2-D standards
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: ETL & UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 2 foot molded patch cord is easy to connect into high density panels with many cables; Compatible w/Cat5e; Available w/Snagless boots for easy wiring conduit installation
- SPECS: Length: 2ft (60cm) | Color: Green | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | ETL Verified | Warranty: Lifetime

---

### Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 pair UTP

---

Tipo guaina cavo	PVC - Polyvinyl Chloride
Classe di resistenza al fuoco	Classe CMG (uso generale)
Standard cablaggio	TIA/EIA-568-B.1-2001 T568B

---

**Prestazioni**

Certificato ETL	Sì
Classe cavo	CAT6 - 250 MHz

---

**Connettore/i**

Connettore A	1 - RJ-45
Connettore B	1 - RJ-45

---

**Caratteristiche fisiche**

Colore	Verde
Diametro filo	24 AWG
Tipo di conduttore	Rame intrecciato
Lunghezza del cavo	2.0 ft [0.6 m]
Lunghezza prodotto	2.0 ft [0.6 m]
Peso prodotto	1.1 oz [31 g]

---

**Informazioni confezione**

Quantità confezione	1
Lunghezza Confezione	6.3 in [15.9 cm]
Larghezza del Pacco	7.9 in [20 cm]
Altezza del Pacco	0.7 in [1.7 cm]
Peso spedizione (confezione)	1.5 oz [42.0 g]

---

**Contenuto della confezione**

Incluso nella  
confezione

1 - 2 ft. Cat6 Patch Cable - Green

---

Informazioni sulla  
garanzia

Warranty

A vita

---

\* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.

