

1U Fixed Server Rack Mount Shelf - 10in Deep Steel Universal Cantilever Tray for 19" AV/ Network Equipment Rack - Heavy Duty Steel - Weight Capacity 44lbs/20kg, Black

**Product ID:** CABSHELF1U10



This 1U rack shelf lets you add 10 in. of flat storage space to any EIA-310 compliant server rack or cabinet.

The durable fixed-rack shelf can hold up to 20 kg (44 lbs.) of equipment and is constructed using SPCC commercial-grade cold-rolled steel.

The 1U cantilever shelf lets you optimize your working space by giving you the ability to mount equipment to your rack instead of taking up desk or floor space. It's perfect for your SOHO (small office, home office) environment, server room or any other location with limited space available.

You can install the 1U rack shelf in your rack at any height, giving you a stable surface for placing equipment that's un-mountable or storing your tools.

The CABSHELF1U10 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Supply additional storage space for mission-critical hardware and non-rackmount equipment

## Features

- **UNIVERSAL COMPATIBILITY:** 19" EIA/ECA-310 compliant 1U 10" deep server rack cabinet shelf for universal fit in any existing server/AV rack or cabinet; Includes M6 Cage nuts & screws for mounting
- **DURABLE DESIGN:** Heavy-duty cantilever shelf tray that is easy to install, constructed of durable 16 gauge SPCC commercial cold-rolled steel with support for weight up to 44 lbs (20kg)
- **STRUCTURAL INTEGRITY:** Constructed with downward facing front and rear lips that uses up minimal height space preserving vertical shelf space for your equipment; Downward lips will not interfere when placing or taking equipment on or off the shelf
- **INSTALLS IN ANY RACK BRAND:** The shelf is fully compatible with our full array of server / network cabinets and enclosures, and other brands like: HP, APC, Dell & Lenovo
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 1U server rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No
Industry Standards	EIA/ECA-310-E

#### Performance

Weight Capacity (Stationary)	44.1 lb [20 kg]
------------------------------	-----------------

#### Special Notes / Requirements

Note	Includes 4x C-cup washers
------	---------------------------

#### Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.4 in [44.3 cm]
Product Length	9.8 in [25 cm]
Product Width	18.3 in [46.5 cm]
Product Height	1.7 in [4.3 cm]

Weight of Product	4.4 lb [2.0 kg]
-------------------	-----------------

---

#### Packaging Information

Package Quantity	1
Package Length	20.5 in [52.0 cm]
Package Width	10.6 in [26.8 cm]
Package Height	2.2 in [5.6 cm]
Shipping (Package) Weight	5.3 lb [2.4 kg]

---

#### What's in the Box

Included in Package	4 - M6 Screws
	1 - 1U Fixed Shelf
	4 - M6 Cage Nuts

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*