

## 2U 19" 2-Post Network Rack Shelf - 20in Deep Center Mount Cantilever Tray Rackmount Shelf for AV/Data Equipment with Cage Nuts & Screws 75lb Weight Capacity

**Product ID:** CABSHF2POST2



The 2 post server rack shelf allows you to add a high capacity mid-mount fixed shelf to almost any standard 2 post server rack.

Our 2U rack shelf is EIA 310 compliant meaning it can fit most standard 19" 2 post racks. The included mounting brackets can be adjusted to accommodate different post depths, making this center mount rack shelf a universal solution for 2 post rack storage.

Constructed using SPCC commercial grade cold-rolled steel, this durable 2 post network rack shelf can hold up to 75 lb. (34 kg) of equipment - a perfect solution for storing non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- For use with most 19" wide, 2 post server racks

## Features

- **UNIVERSAL COMPATIBILITY:** 2U 19" network rack shelf 20" deep for universal fit in any existing EIA 30 compliant 2 Post rack & includes M6 Cage nuts & screws for mounting shelf
- **CENTER MOUNT SHELF:** Center-mount design allows equipment on the drawer to sit forward of the posts of the rack for easier installation and routing of cables
- **DURABLE DESIGN:** Heavy duty double sided cantilever tray is constructed using durable 14 SPCC commercial cold rolled grade steel and can hold equipment up to 75 lb. (34 kg)
- **EASY ACCESS:** Can be used for modems, routers, wi-fi access points, and other IT/network/telco equipment that can't be mounted in a rack, or to store and access frequently used tools and supplies
- **LIFETIME WARRANTY:** StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

---

### Hardware

Warranty	Lifetime
U Height	2U
Cable Management	No
Industry Standards	EIA/ECA-310-E
	EIA/ECA-310-E

---

### Performance

Weight Capacity (Stationary)	75.0 lb [34 kg]
---------------------------------	-----------------

---

### Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.2 in [43.6 cm]
Product Length	20.0 in [50.8 cm]
Product Width	19.0 in [48.3 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	8.8 lb [4.0 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	21.7 in [55.2 cm]
Package Width	21.7 in [55.0 cm]
Package Height	5.2 in [13.2 cm]
Shipping (Package) Weight	11.4 lb [5.2 kg]

---

**What's in the Box**

Included in Package	1 - Rack Shelf
	4 - M6 Screws
	4 - M6 Cage Nuts
	4 - M6 Plastic Cup Washers

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*