

2U Server Rack Shelf - Universal Rack Mount Cantilever Shelf for 19" Network Equipment Rack & Cabinet - Heavy Duty Steel – Weight Capacity 50lb/23kg - 22" Deep Tray, Black - TAA

Product ID: CABSHELF22



The CABSHELF22 2U 22in Depth Fixed Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Our high-quality rack shelves are designed to withstand harsh work environments with ease. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- **UNIVERSAL 19" FIT:** This 2U server rack shelf is designed to fit any 19" wide server rack or enclosure including major brands like APC, Dell, Lenovo, HPE and can accommodate your data, IT, networking or other equipment up to 22" (56cm) deep
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures long term durability and supports a total weight of 50lbs/23kg making it the perfect rack shelf solution for any environment
- **STRUCTURAL INTEGRITY:** Constructed with downward facing front and rear lips that uses up minimal height space preserving vertical shelf space for your equipment; Downward lips will not interfere when placing or taking equipment on or off the shelf
- **VERSATILE FUNCTIONALITY:** At 22in deep, this fixed rackmount shelf is designed to work with any 19 inch cabinet or equipment rack; it provides additional storage space for mission critical hardware, and can even store your tools or audio/video accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 2U server rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Mounting Options	Front Mount (Front Only)

Performance

Weight Capacity (Stationary)	49.9 lb [22.6 kg]
------------------------------	-------------------

Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.1 in [1.6 mm]
Internal Width	17.4 in [44.3 cm]
Product Length	22.0 in [55.9 cm]
Product Width	18.3 in [46.5 cm]
Product Height	3.5 in [8.8 cm]

Weight of Product	8.2 lb [3.7 kg]
-------------------	-----------------

Packaging Information

Package Quantity	1
Package Length	23.0 in [58.5 cm]
Package Width	22.6 in [57.3 cm]
Package Height	4.4 in [11.2 cm]
Shipping (Package) Weight	11.1 lb [5.0 kg]

What's in the Box

Included in Package	1 - 2U rack shelf
	4 - M5 screws
	4 - M5 cage nuts
	1 - instruction manual

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***