

2U Server Rack Shelf - Universal Rack Mount Cantilever Shelf for 19" Network Equipment Rack & Cabinet - Heavy Duty Steel - Weight Capacity 44lb/20kg - 16" Deep Tray

Product ID: CABSHELF



The Black CABSHELF Standard Universal Server Rack Cabinet Shelf helps to efficiently organize your mission critical computer hardware and accessories by adding a fixed shelf with the capacity to hold up to 20 kg (44 lbs).

Universally mountable in any standard front mount 19" server rack or cabinet, the rack shelf is constructed of sturdy, cold-rolled steel for long-term durability.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware

Features

- **UNIVERSAL 19" FIT:** This 2U server rack shelf is designed to fit any 19" wide server rack or enclosure including major brands like APC, Dell, Lenovo, HPE and can accommodate your data, IT, networking or other equipment up to 15.7" (40cm) deep

- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy front mounted cabinet shelf ensures long term durability and supports a total weight of 44lbs/20kg making it the perfect rack shelf solution for any environment
- **STRUCTURAL INTEGRITY:** Constructed with downward facing front and rear lips that uses up minimal height space preserving vertical shelf space for your equipment; Downward lips will not interfere when placing or taking equipment on or off the shelf
- **VERSATILE FUNCTIONALITY:** At 16in deep, this fixed rackmount shelf is designed to work with any 19 inch cabinet or equipment rack; it provides additional storage space for mission critical hardware, and can even store your tools or audio/video accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 2U server rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
U Height	2U
Cable Management	No

Performance

Weight Capacity (Stationary)	44.1 lb [20 kg]
------------------------------	-----------------

Physical Characteristics

Color	Black
Internal Width	17.4 in [44.3 cm]
Internal Depth	15.7 in [40 cm]
Product Length	16.0 in [40.6 cm]
Product Width	18.9 in [48.0 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	5.1 lb [2.3 kg]

Packaging Information

Package Quantity	1
Package Length	19.4 in [49.4 cm]

Package Width	22.4 in [57.0 cm]
Package Height	6.4 in [16.3 cm]
Shipping (Package) Weight	6.9 lb [3.1 kg]

What's in the Box

Included in Package	4 - M6 Screws
	4 - M6 Cage Nuts
	1 - 2U Rack Shelf
	1 - Quick-Start Guide

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***