

3 Port CardBus 1394a FireWire Adapter Card - Digital Video Editing Kit

Product ID: CB1394



This 3 Port PCMCIA IEEE 1394 FireWire 400 Laptop Adapter Card allows you to connect FireWire/i.LINK devices such as iPods or DV (digital video) camcorders to your laptop computer through a CardBus slot.

Compatible with both PC and Mac laptop computers, the adapter card supports hot-swapping FireWire device connections, allowing you to unplug and swap peripherals with ease.

The adapter card includes a 5ft FireWire cable as well as a copy of ULEAD's VideoStudio SE Basic video editing software (Windows only), making it easy to capture and edit video on your notebook computer, directly from your digital video camcorder.

Certifications, Reports and Compatibility



Applications

- iPods/MP3 players
- Portable hard drives
- External CDR-CDRW drives

- DVD drives
- Digital cameras
- Digital camcorders (compatible with Sony, Canon, Panasonic, JVC, Samsung models)
- Scanners
- Printers

Features

- Includes everything needed to edit your own home movies, add scene transitions and other effects with the included ULEAD VideoStudio SE software
- High speed data transfer rates of up to 400 Mbits/sec.
- Hot swap capabilities allows you to connect or disconnect devices without turning off your laptop
- Low power consumption preserves laptop computer battery life
- Connect up to 63 devices by cascading multiple hubs

Hardware

Warranty	Lifetime
Ports	3
Interface	FireWire 400 (1394a)
Bus Type	CardBus (PCMCIA)
Industry Standards	OHCI
	IEEE 1394-1995
	1394A
Chipset ID	VIA/VLI - VT6306

Performance

Maximum Data Transfer Rate	400 Mbps
----------------------------	----------

Connector(s)

Connector Type(s)	3 - FireWire 400 (6 pin, IEEE 1394a)
-------------------	--------------------------------------

1 - PC Card (Type II, Cardbus)

Software

OS Compatibility	Windows 98SE/ ME/ 2000/ XP (32/64-bit)/ Server 2003 (32/64-bit)/ Vista (32/64-bit)/ 7 (32/64-bit) , Mac OS 8.6 ~10.4, Linux
------------------	---

Special Notes / Requirements

System and Cable Requirements	32-bit CardBus Compatible PCMCIA Type II slot
Note	Separate power adapter only required if connecting high-powered FireWire device(s) that draw more power than CardBus slot can provide.

Power

Power Source	Not Included (not required for standard applications)
Output Voltage	12V DC
Output Current	1A+
Center Tip Polarity	Positive

Physical Characteristics

Product Length	4.5 in [11.5 cm]
Product Width	2.1 in [5.4 cm]
Product Height	2.0 in [5 cm]
Weight of Product	4.9 oz [140 g]

Packaging Information

Package Length	8.3 in [21 cm]
Package Width	1.4 in [36 mm]
Package Height	5.7 in [14.4 cm]
Shipping (Package) Weight	0.5 lb [0.2 kg]

What's in the Box

Included in Package	1 - CardBus FireWire Card
---------------------	---------------------------

1 - FireWire 6-pin to 4-pin cable

1 - VideoStudio software CD

1 - Instruction Manual

**Warranty
Information**

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***